



H K Wentworth Group
Distributed and Supported in
the UK



hakko.com - hakko.co.uk

Packing List



FG100B Unit + Instructions



006P 9 V dry battery (for trial)



191-212 Sensor Wires (10 pack)

FG100B



Specifications:

FG100B

Power Supply	006P 9V dry battery (alkaline cell recommended)
Temperature resolution	1°C
Temperature measurement range	0 to 700°C
Temperature precision	±3°C (300 to 600°C)
±5°C (other than above)	Composite heater
Temperature sensor	K (CA)type thermocouple
Display	LCD : 3 1/2 digits
Operating environment	Ambient temperature/humidity range : 0 to 40°C, max.80% RH (without condensation)
Environmental conditions	Applicable rated pollution degree 2 (According to IEC/UL 61010-1)
Dimensions	68(W)×140(H)×38(D) mm
Weight	125g

* Dimensions : excluding protrusions

* Weight (excluding battery)

Recommended Extras:



A1310
Solder Pot Probe



C1541
Hot Air Station Probe




MAX HOLD

AUTO HOLD

Temperature Measurement Count Function
Up to 999 times

Display contents

Display temperature/
Burnout alarm^{*1}
(When "-1" is displayed, burnout)
Battery low alarm^{*2}



*1 This alarm indicates a sensor burnout. If this alarm occurs, replace the sensor.

*2 When **B** appears, be sure to replace the battery. Failure to do so will result in incorrect temperature measurements.

*3 When pressing the **MAX HOLD** and **AUTO HOLD** button for longer, the count is reset.



H K Wentworth Group
Distributed and Supported in
the UK