

PRODUCT-DETAILS

CA5-22E

CA5-22E Auxiliary Contact Block



General Information

Extended Product Type	CA5-22E
Product ID	1SBN010040R1022
EAN	3471522121103
Catalog Description	CA5-22E Auxiliary Contact Block
Long Description	CA5-22E Auxiliary Contact Block

Ordering

EAN	3471522121103
Minimum Order Quantity	2 piece
Customs Tariff Number	85389099

Dimensions

Product Net Width	44 mm
Product Net Height	47 mm
Product Net Depth / Length	39 mm
Product Net Weight	0.06 kg

Container Information

Package Level 1 Units	2 piece
Package Level 1 Width	65 mm
Package Level 1 Height	43 mm
Package Level 1 Depth / Length	129.5 mm
Package Level 1 Gross Weight	0.12 kg
Package Level 1 EAN	3471522121103
Package Level 2 Units	box 200 piece
Package Level 2 Width	300 mm
Package Level 2 Height	308 mm
Package Level 2 Depth / Length	245 mm
Package Level 2 Gross Weight	12 kg
Package Level 3 Units	3600 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Additional Information

Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Maximum Electrical Switching Frequency	1200 cycles per hour
Maximum Mechanical Switching Frequency	3600 cycles per hour
Mechanical Durability	10 million 3 million
Minimum Switching Capacity	A9 ... A75 17 / 5 VLT4K A95 ... A110 24 / 50 VLT4K
Mounting on Contactors	A 9...A 75
Mounting Position	Front face
Mounting Type	Front mounting
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts NO	2
Order Multiple	2 piece
Power Loss	at Rated Operating Conditions per Pole 0.1 W
Product Main Type	Accessories for Block Contactors
Product Name	Auxiliary Contact Block
Rated Breaking Capacity acc. to IEC 60947-5-1	10 x Ie AC-15
Rated Frequency (f)	Supply Circuit 50 60 Hz
Rated Insulation Voltage (U _i)	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Making Capacity acc. to IEC 60947-5-1	10 x Ie AC-15
Rated Operational Current AC-15 (I _e)	(220 / 240 V) 4 A (24 V) 6 / 144 A (380 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Rated Operational Current DC-13 (I _e)	(125 V) 0.55 / 69 A (24 V) 6 / 144 A (250 V) 0.3 / 75 A (48 V) 2.8 / 134 A (72 V) 1 / 72 A

Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 24 V
Remarks	100
RoHS Date	20171115
Suitable For	A9 A16 A26 A50 A63 A75 A95 A110 AL9 AL16 AL26 AE45 AE50 AE63 AE75 TAL9 TAL16 TAL26 AF45 AF50 AF63 AF75 TAE45 TAE50 TAE75 UA50 UA63 UA75 UA95 UA110 GA75 GAE75
Terminal Type	Screw Terminals

Certificates and Declarations (Document Number)

CB Certificate	CB_SE_62119
CCC Certificate	CCC_2015010304800518
CSA Certificate	CSA_1033838
Data Sheet, Technical Information	1SBC100122C0202_Ch04
Declaration of Conformity - CE	1SBD250809U1000
DNV GL Certificate	DNV_GL_TAE00001UT
EAC Certificate	EAC_RU C-FR ME77 B03391
Environmental Information	1SBD250132E1001
GOST Certificate	GOST_POCCFRME77B07175
Instructions and Manuals	1SBC101012M5501
RINA Certificate	RINA_ELE128713XG001
RoHS Information	1SBD250809U1000
UL Certificate	UL_071301E48139

Classifications

ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC002498 - Accessories for low-voltage switch technology
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
Object Classification	K

Code	
UNSPSC	39121500
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors Accessories

