

## Warning label - PML-W200 (50X50)R - 0830452

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Warning label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 50 x 50 mm, Number of individual labels: 500

### Your advantages

- ✓ The color preprinted PML warning labels without symbols allow you to create custom warning instructions. The PROJECT complete software offers a wide range of symbols
- ✓ The label consists of soft, highly flexible PVC film that molds itself to uneven surfaces
- ✓ The warning labels conform to the ISO 7010 international standard
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ Labeling service: Phoenix Contact can custom-label all PML-W ... markers in accordance with your requirements

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 717762
GTIN	4046356717762
Weight per Piece (excluding packing)	455.000 g
Custom tariff number	39199080
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	50 mm
Width (a)	50 mm
Height (c)	59.25 mm
Diameter	0.00 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------

# Warning label - PML-W200 (50X50)R - 0830452

## Technical data

### Ambient conditions

Ambient temperature (assembly)	> 8 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

### General

Color	yellow/black
Type	Triangle
Components	Silicone-free
Material	PVC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	1
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146231 THERMOMARK X1.2
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	50 µm
Marking mounting type	adhesive

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Environmental Product Compliance

	Reaction mass of DOTE and MOTE
--	--------------------------------

## Classifications

### eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	40200100

## Warning label - PML-W200 (50X50)R - 0830452

### Classifications

#### eCl@ss

eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27141100
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

#### ETIM

ETIM 3.0	EC001694
ETIM 4.0	EC001777
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718
UNSPSC 21.0	55121718

### Accessories

#### Accessories

##### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printer for printing product groups TML..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP..., EMLF..., PML..., and PMM..., width: 110 mm, color: black