


RC module - EMG 15-RC/220UF/330R - 2311072

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Filter module for parallel debouncing of two relay contacts



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	50 pc
GTIN	 4 046356 137829
GTIN	4046356137829
Weight per Piece (excluding packing)	41.950 g
Custom tariff number	85363010
Country of origin	Germany

Technical data

Dimensions

Width	15 mm
Height	75 mm
Depth	55 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

General

Nominal voltage (Phase voltage)	24 V AC/DC (1 ampere / relay contact)
Resistor in RC combination	330 Ω
Capacitor in RC combination	220 µF
Mounting position	any

Standards and Regulations

Designation	Air clearances and creepage distances
Standards/regulations	DIN EN 50178
Pollution degree	2
Overvoltage category	II

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

RC module - EMG 15-RC/220UF/330R - 2311072

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27210100
eCl@ss 4.1	27210100
eCl@ss 5.0	27371000
eCl@ss 5.1	27371000
eCl@ss 6.0	27371000
eCl@ss 7.0	27371010
eCl@ss 8.0	27371010
eCl@ss 9.0	27371010

ETIM

ETIM 5.0	EC000683
ETIM 6.0	EC000683
ETIM 7.0	EC000683

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	39121008
UNSPSC 18.0	32151504
UNSPSC 19.0	32151504
UNSPSC 20.0	32151504
UNSPSC 21.0	32151504

Approvals

Approvals

Approvals

EAC

Ex Approvals

RC module - EMG 15-RC/220UF/330R - 2311072

Approvals

Approval details

EAC		RU C- DE.A*30.B.01082
-----	---	--------------------------