

## Electronic housing - EMG 17-LG - 2946078

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Electronic housing, with universal foot, for p.c.b. insertion, without screw connection terminal blocks and cover, pitch 5

### Your advantages

- ✓ Choice of four cover sizes in transparent or color versions
- ✓ Practical and easy-to-wire conductor connections
- ✓ High degree of flexibility due to the wide choice of versions
- ✓ Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- ✓ Uniform and appropriate housing technology
- ✓ User-friendly and safe mounting on DIN rails according to EN 60715
- ✓ Inflammability class V0 insulation material (according to UL 94)
- ✓ Shock and contamination-proof accommodation of electronic components
- ✓ Universal PCBs for all pitches

### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 082031
GTIN	4017918082031
Weight per Piece (excluding packing)	17.000 g
Custom tariff number	85472000
Country of origin	Germany

### Technical data

#### General

Housing type	Component housing
Housing material	Polycarbonate fiber reinforced
Color (RAL)	green

# Electronic housing - EMG 17-LG - 2946078

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Dimensions

Length	75 mm
Height	47.5 mm
Width	17.5 mm
Pitch	5 mm
Depth	75 mm

### Technical data

Power dissipation without gap	1.3 W
Power dissipation with 20 mm gap	1.4 W
Number of positions	6

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section flexible max.	2.5 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	8 mm

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----


### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings


# Electronic housing - EMG 17-LG - 2946078

Dimensional drawing



1 = Top edge of the PCB  
 B = Housing width

Dimensional drawing



Pitch 5 mm  
 a = Area for mounting components, 38 mm in the hood  
 b = Area for mounting components, 45 mm in the housing

# Electronic housing - EMG 17-LG - 2946078

## Classifications

### eCl@ss

eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

# Electronic housing - EMG 17-LG - 2946078

## Approvals

EAC		B.01742
-----	--	---------

## Accessories

### Accessories

#### Filler plug

#### Electronic housing - EMG-KA - 2941510



Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.

---

## PCB

#### PCB - P 1-EMG 17 - 2946120



PCB for assembling electronic components

---

#### Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

---

#### Marking material - EMG-SGKS 10 - 2947585



Equipment marker, narrow

## Electronic housing - EMG 17-LG - 2946078

### Accessories

Marking material - EMG-SGKS 10 - 2947585



Equipment marker, narrow

---

Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

---

### Necessary add-on products

Covering hood - EMG 17-H 7,5MM KLAR - 2946094



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm, width: 17 mm

---

Covering hood - EMG 17-H 15MM KLAR - 2946104



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 17 mm

---

Electronic housing - EMG 17-H 35MM KLAR - 2942221



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 35 mm, width: 17 mm

---

## Electronic housing - EMG 17-LG - 2946078

### Accessories

Covering hood - EMG 17-H 52MM GN - 2946117



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 17.5 mm