

Plastic label - US-EMLP (27X15) SR - 0828894

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic label, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 27 x 15 mm, Number of individual labels: 27



Your advantages

- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers are easy to separate and can be easily fitted
- The sheets provide space for including function texts



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	
GTIN	4046356558976
Weight per Piece (excluding packing)	17.810 g
Custom tariff number	39199080
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	14.9 mm
Width (a)	26.9 mm
Height (c)	0.5 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Plastic label - US-EMLP (27X15) SR - 0828894

Technical data

General

Color	silver
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	27
Number of individual labels per row	3
Adhesive	Acrylic
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	500 µm
Adhesive strength	50 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129

Plastic label - US-EMLP (27X15) SR - 0828894

Classifications

eCl@ss

eCl@ss 9.0	27400629
------------	----------

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

CSA

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	70191766
-----	--	---	----------

Accessories

Accessories

Magazine

Plastic label - US-EMLP (27X15) SR - 0828894

Accessories

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards

Marker carriers

Marker carriers - CARRIER-EMP 22 (27X15) - 0827447



Marker carriers, black, unlabeled, mounting type: screw, rivet, diameter: 22 mm, lettering field size: 27 x 15 mm

Marker carriers - CARRIER-EMLP 22 (27X15) - 0828986



Marker carriers, black, unlabeled, mounting type: screw, rivet, diameter: 22 mm, lettering field size: 27 x 15 mm
