

## Plastic label - US-EMLP-HA (60X30) - 0830990

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 60 x 30 mm, Number of individual labels: 4



### Your advantages

- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- ✓ The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties
- ✓ The perforated markers are easy to separate and can be easily fitted
- ✓ The sheets provide space for including function texts

### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	
GTIN	4046356949606
Weight per Piece (excluding packing)	18.860 g
Custom tariff number	39199080
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	30 mm
Width (a)	60 mm
Height (c)	0.5 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

#### General

## Plastic label - US-EMLP-HA (60X30) - 0830990

### Technical data

#### General

Color	white
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	4
Number of individual labels per row	1
Adhesive	Acrylic
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	500 µm
Marking mounting type	adhesive

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

### Drawings

# Plastic label - US-EMLP-HA (60X30) - 0830990

Pictogram



## Classifications

### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

### ETIM

ETIM 4.0	EC000761
----------	----------

# Plastic label - US-EMLP-HA (60X30) - 0830990

## Classifications

### ETIM

ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

### UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

## Approvals

### Approvals

Approvals

CSA

Ex Approvals

### Approval details

CSA		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	70191766
-----	--	---	----------

## Accessories

### Accessories

#### Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards