

## Cable marker - WMTB HF (40X12)R RD - 0803314

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker, Roll, red, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: Assembly with cable binders, cable diameter:  $\geq 6$  mm, lettering field size: 40 x 12 mm, Number of individual labels: 1000

### Your advantages

- The marker has two fastening eyes so that it can be attached to the conductor using WT ... cable ties
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.

### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626024332
Weight per Piece (excluding packing)	1,060.600 g
Custom tariff number	39204910
Country of origin	Denmark
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	40 mm
Width (a)	12 mm

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

#### General

Color	red
Type	Roll

# Cable marker - WMTB HF (40X12)R RD - 0803314

## Technical data

### General

Components	halogen-free
Flammability rating according to UL 94	V0
Material	PUR
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1000
Number of individual labels per row	1
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146231 THERMOMARK X1.2
	0804501 THERMOMARK ROLLMASTER 300
	0804663 THERMOMARK ROLLMASTER 600
Ink ribbon	5148007 THERMOMARK-RIBBON 110-WMTB HF
	0802990 TM-RIBBON 110-WMTB HF WH
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Note	The information does not apply to the color fastness of the material.
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result of wipe resistance test	Test passed
Marking mounting type	Assembly with cable binders

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

### Classifications

#### eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401

## Cable marker - WMTB HF (40X12)R RD - 0803314

### Classifications

#### eCl@ss

eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

#### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

#### UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

##### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

Ink ribbon - TM-RIBBON 110-WMTB HF WH - 0802990



Ink ribbon, for roll printer for printing product group WMTB HF..., width: 110 mm, color: white