

Data logger - PSK RTU 50 - 2400018

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Data logger with integrated GSM/GPRS modem, 2 analog and 4 digital inputs, 4 digital outputs, 1 serial interface, and 1 Ethernet interface



Product Description

The PSK RTU 50 is a data logger with integrated GSM/GPRS modem, 2 analog and 4 digital inputs, 2 digital outputs, 1 serial interface, and 1 Ethernet interface. Thanks to the innovative power management, the data logger can also be operated with batteries or solar cells.

Your advantages

- ✓ Alarm inputs and switching outputs
- ✓ Integrated GSM/GPRS modem
- ✓ LED diagnostic indicators
- ✓ Data logger, gateway, and alarm manager
- ✓ Low power consumption

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 016429
GTIN	4055626016429
Weight per Piece (excluding packing)	475.000 g
Custom tariff number	84719000
Country of origin	Netherlands
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	210 mm
Height	110 mm
Depth	45 mm

Ambient conditions

Data logger - PSK RTU 50 - 2400018

Technical data

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Shock	25g, Criterion 1, according to IEC 60068-2-27
Vibration (operation)	5g

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Interference emission	Noise emission test as per EN 61000-6-4 EN 55011 (emitted interference) Class A
Noise immunity	Noise immunity test in accordance with EN 61000-6-2 Electromagnetic fields EN 61000-4-3/IEC 61000-4-3 EN 61000-4-3 (radiated noise immunity) Criterion A, 10 V/m
Immunity to surge	Noise immunity test in accordance with EN 61000-6-2 Transient overvoltage (surge) EN 61000-4-5/IEC 61000-4-5 EN 61000-4-5 (surge) Criterion B
Immunity to burst	Noise immunity test in accordance with EN 61000-6-2 Fast transients (burst) EN 61000-4-4/IEC 61000-4-4 EN 61000-4-4 (EFT burst) Criterion B; Supply lines: 2 kV; Signal/data lines: 2 kV
Immunity to ESD	Noise immunity test in accordance with EN 61000-6-2 Electrostatic discharge (ESD) EN 61000-4-2/IEC 61000-4-2 EN 61000-4-2 (ESD) Criterion B, 6 kV contact discharge, 8 kV air discharge
Immunity to conducted interference	Noise immunity test in accordance with EN 61000-6-2 Conducted interference EN 61000-4-6/IEC 61000-4-6 EN 61000-4-6 (line noise immunity) Criterion A, Test voltage 10 V
Noise emission	EN 61000-6-4
Vibration (storage/transport)	5g
Shock	25g, Criterion 1, according to IEC 60068-2-27
Vibration (operation)	5g

Data interfaces

Interface	RS-232
	RS-232/-485
	Serial
Protocols supported	IEC 60870-5-101, Modbus/RTU, IEC 62056-21
	IEC 60870-5-104, Modbus TCP/IP, FTP
Interface	Ethernet
Connection method	RJ45
Interface description	GSM / GPRS
Minimum frequency	850 MHz
Max. frequency	1900 MHz

Data logger - PSK RTU 50 - 2400018

Technical data

Data interfaces

Number	1
Connection method	SMA (female)
Resistance	50 Ω
SIM Interface	1.8 volt and 3 volt SIM card

Power supply

Typical current consumption	5 mA
Max. current consumption	100 mA
Supply voltage	24 V DC
Supply voltage range	10 V DC ... 30 V DC
Power dissipation	max. 0.12 W
Battery capacity	235 mAh
Battery voltage	3 V DC
Service life of battery	6 years

Direct I/Os

Number of inputs	4
Connection technology	COMBICON
Output name	Digital outputs
Number of outputs	2 (Relay output)
Number of inputs	2
Connection method	COMBICON connectors
Connection technology	Screw connection

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Articles in set

Data logger - PSK RTU 50 - 2400018

Data logger with integrated GSM/GPRS modem, 2 analog and 4 digital inputs, 4 digital outputs, 1 serial interface, and 1 Ethernet interface



Classifications

eCl@ss

eCl@ss 5.0	27242700
eCl@ss 5.1	27242700

Data logger - PSK RTU 50 - 2400018

Classifications

eCl@ss

eCl@ss 6.0	27242200
eCl@ss 7.0	27242205
eCl@ss 8.0	27242205
eCl@ss 9.0	27242205

ETIM

ETIM 4.0	EC001422
ETIM 5.0	EC001422
ETIM 6.0	EC001422
ETIM 7.0	EC001422

Accessories

Accessories

Antenna

Antenna - PSI-GSM/UMTS-QB-ANT - 2313371



GSM UMTS antenna, with omnidirectional characteristic, 2 m antenna cable with SMA round connector

Programming cable

Cable for programming - PSK RTU PRG CAB - 2402816



Programming cable for PSK RTU 50