


Interface module - UM-D15SUB-F/KDS3-PMT/SC061 - 2906275


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with 15-pos. D-SUB socket strip and screw connection with knife disconnection, for mounting on NS 35/7,5 or NS 32



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 055626 057323 |
| GTIN | 4055626057323 |
| Weight per Piece (excluding packing) | 194.000 g |
| Custom tariff number | 85369010 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|--------|-------|
| Width | 87 mm |
| Height | 90 mm |
| Depth | 59 mm |

Ambient conditions

| | |
|---------------------------------|--------------------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Degree of protection | IP00 |
| | ≥ IP54 (Installation location) |

General

| | |
|---------------------------------|---------|
| Nominal voltage U_N | 25 V AC |
| | 60 V DC |
| Max. perm. current (per branch) | 2 A |

Interface module - UM-D15SUB-F/KDS3-PMT/SC061 - 2906275

Technical data

General

| | |
|---|-----|
| Max. permissible current (all branches) | 4 A |
| Number of positions | 15 |
| Mounting position | any |

Connection data

| | |
|----------------------------------|---|
| Connection name | Field level |
| Connection method | Screw connection with disconnect knife |
| Number of positions | 15 |
| Conductor cross section solid | 0.2 mm ² ... 4 mm ² |
| Conductor cross section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross section AWG | 24 ... 12 |

Connection data 2

| | |
|-----------------------|------------------|
| Connection name | Controller level |
| Connection method | D-SUB-15 socket |
| Number of connections | 1 |
| Number of positions | 15 |

Standards and Regulations

| | |
|--------------------------|---------------------------------------|
| Designation | Air clearances and creepage distances |
| Standards/regulations | DIN EN 50178: 1998-04 |
| Rated insulation voltage | 125 V |
| Rated surge voltage | 1.2 kV (1.2/50 µs) |
| Insulation | Functional insulation |
| Pollution degree | 2 |
| Overvoltage category | II |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250313 |
| eCl@ss 4.1 | 27250313 |
| eCl@ss 5.0 | 27250313 |
| eCl@ss 5.1 | 27250313 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |
| eCl@ss 9.0 | 27141152 |

Interface module - UM-D15SUB-F/KDS3-PMT/SC061 - 2906275

Classifications

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC002780 |
| ETIM 6.0 | EC002780 |
| ETIM 7.0 | EC002780 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39121421 |
| UNSPSC 18.0 | 39121432 |
| UNSPSC 19.0 | 39121432 |
| UNSPSC 20.0 | 39121432 |
| UNSPSC 21.0 | 39121432 |