

Interface module - VIP-2/PT/D37SUB/M - 2904277

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with push-in connection and plug D-SUB miniature pin strip, for mounting on NS 35 rails, 37-pos.

Your advantages

- ✔ These VARIOFACE modules are used in combination with the relevant front adapters



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 812580 |
| GTIN | 4046356812580 |
| Weight per Piece (excluding packing) | 212.500 g |
| Custom tariff number | 85366990 |
| Country of origin | United States |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|--------|----------|
| Width | 102.8 mm |
| Height | 72.1 mm |
| Depth | 46.6 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 70 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

General

| | |
|---------------------------------|---------|
| Nominal voltage U_N | 25 V AC |
| | 60 V DC |
| Max. perm. current (per branch) | 2 A |

Interface module - VIP-2/PT/D37SUB/M - 2904277

Technical data

General

| | |
|---------------------|-----|
| Number of positions | 37 |
| Status display | No |
| Mounting position | any |

Connection data

| | |
|----------------------------------|--|
| Connection name | Field level |
| Connection in acc. with standard | IEC / EN |
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Number of positions | 37 |
| Conductor cross section solid | 0.14 mm ² ... 4 mm ² |
| Conductor cross section flexible | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross section AWG | 26 ... 14 |

Connection data 2

| | |
|-----------------------|------------------|
| Connection name | Controller level |
| Connection method | D-SUB pin strip |
| Number of connections | 1 |
| Number of positions | 37 |

Supported controller

| | |
|---------------------|--------------------------------------|
| Controller | HONEYWELL Experion PKS C300/C-Series |
| - suitable I/O card | TDIL01 (non-redundant) |
| | TDIL11 (redundant) |
| | TDOB01 (non-redundant) |
| | TDOB11 (redundant) |
| | TAIX01 (non-redundant) |
| | TAIX11 (redundant) |
| | TAOX01 (non-redundant) |
| | TAOX11 (redundant) |

Standards and Regulations

| | |
|----------------------------------|----------|
| Connection in acc. with standard | CSA |
| Standards/regulations | EN 50178 |
| Rated surge voltage | 1.2 kV |
| Pollution degree | 2 |
| Overvoltage category | II |


Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Interface module - VIP-2/PT/D37SUB/M - 2904277

Drawings

Circuit diagram



Connection scheme VIP-2/SC/D37SUB/M

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250300 |
| eCl@ss 4.1 | 27250300 |
| eCl@ss 5.0 | 27250300 |
| eCl@ss 5.1 | 27250300 |
| eCl@ss 6.0 | 27242600 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |
| eCl@ss 9.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC002780 |
| ETIM 5.0 | EC002780 |
| ETIM 6.0 | EC002780 |
| ETIM 7.0 | EC002780 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211824 |
| UNSPSC 7.0901 | 39121421 |
| UNSPSC 11 | 39121421 |
| UNSPSC 12.01 | 39121421 |
| UNSPSC 13.2 | 39121432 |
| UNSPSC 18.0 | 39121432 |
| UNSPSC 19.0 | 39121432 |
| UNSPSC 20.0 | 39121432 |
| UNSPSC 21.0 | 39121432 |

Interface module - VIP-2/PT/D37SUB/M - 2904277

Approvals


Approvals


Approvals


CSA / UL Recognized / cUL Recognized / CSAus / EAC / cULus Recognized / cCSAus


Ex Approvals

Approval details

| | | | |
|----------------------------|---|---|---------|
| CSA |  | http://www.csagroup.org/services-industries/product-listing/ | 2122203 |
| Nominal voltage UN | | 105 V | |
| Nominal current IN | | 2 A | |
| mm ² /AWG/kcmil | | 26-14 | |

| | | | |
|----------------------------|---|---|---------------|
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 2 A | |
| mm ² /AWG/kcmil | | 26-14 | |

| | | | |
|----------------------------|---|---|---------------|
| cUL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 2 A | |
| mm ² /AWG/kcmil | | 26-14 | |

| | | | |
|----------------------------|---|---|---------|
| CSAus |  | http://www.csagroup.org/services-industries/product-listing/ | 2122203 |
| Nominal voltage UN | | 105 V | |
| Nominal current IN | | 2 A | |
| mm ² /AWG/kcmil | | 28-14 | |

Interface module - VIP-2/PT/D37SUB/M - 2904277

Approvals

