

## I/O extension module - NLC-IO-2AI-2AO-01 - 2701040

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



I/O extension module for use with Nanoline base unit. Equipped with 2 analog input (0...10 V DC, -10...+10 V DC, 0/4...20 mA) and 2 analog output (0...10 V DC, 0/4...20 mA) channels. A maximum of three I/O extension modules can be attached to a base unit.

### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356629522
Weight per Piece (excluding packing)	199.000 g
Custom tariff number	85389099
Country of origin	India
Note	Made to Order (non-returnable)

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

Width	40 mm
Height	103.5 mm
Depth	43 mm

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

#### Supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 24 V DC

## I/O extension module - NLC-IO-2AI-2AO-01 - 2701040

### Technical data

#### Supply

Supply current	100 mA
----------------	--------

#### Analog inputs

Description of the input	Single ended
Input name	Analog inputs
Number of inputs	2 (Voltage or current can be chosen separately)
Connection method	Individual wires
Connection technology	Screw connection
A/D converter resolution	12 bit
Limit frequency (3 dB)	5 Hz
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA
Input resistance current input	120 Ω
Voltage input signal	0 V ... 10 V
	-10 V ... 10 V
Input resistance of voltage input	200 kΩ

#### Analog outputs

Number of outputs	2
Connection method	Individual wires
Connection technology	Screw connection
Output name	Analog outputs
D/A converter resolution	12 bit
Current output signal	0 mA ... 20 mA
	4 mA ... 20 mA
Load/output load current output	500 Ω
Voltage output signal	0 V ... 10 V
Load/output load voltage output	1000 Ω
Precision	1 %


#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

#### Drawings

# I/O extension module - NLC-IO-2AI-2AO-01 - 2701040

Dimensional drawing



## Classifications

eCl@ss

eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27242700
eCl@ss 5.1	27242700
eCl@ss 6.0	27242200
eCl@ss 7.0	27242216
eCl@ss 8.0	27242216
eCl@ss 9.0	27242216

ETIM

ETIM 2.0	EC001417
ETIM 3.0	EC001417

# I/O extension module - NLC-IO-2AI-2AO-01 - 2701040

## Classifications

### ETIM

ETIM 4.0	EC001417
ETIM 5.0	EC001417
ETIM 6.0	EC001417
ETIM 7.0	EC001417

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39122329
UNSPSC 18.0	39122329
UNSPSC 19.0	39122329
UNSPSC 20.0	39122329
UNSPSC 21.0	39122329

## Approvals

### Approvals

---

Approvals

UL Listed / EAC

---

Ex Approvals

---

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
-----------	--	---	---------------

EAC		EAC-Zulassung
-----	--	---------------