

PRODUCT-DETAILS

# SU202M-C6

## Miniature Circuit Breaker - SU200M - 2P - C - 6 ampere



### General Information

Extended Product Type	SU202M-C6
Product ID	2CDS272337R0064
EAN	4016779931045
Catalog Description	Miniature Circuit Breaker - SU200M - 2P - C - 6 ampere
Long Description	SU202M-C6 Miniature Circuit Breaker C-Char., 10kA, 6A, 2P UL489

### Technical

Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Number of Poles	2
Number of Protected Poles	2
Tripping Characteristic	C
Rated Current ( $I_n$ )	6 A
Rated Operational Voltage	acc. to IEC 60947-2 400 V AC
Power Loss	4 W at Rated Operating Conditions per Pole 2,0 W
Rated Insulation Voltage ( $U_i$ )	acc. to IEC/EN 60664-1 440 V
Rated Frequency (f)	50 Hz 60 Hz DC Hz
Rated Ultimate Short-	(400 V AC) 15 kA

Circuit Breaking Capacity ( $I_{cu}$ )	
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(400 V AC) 11.2 kA
Overvoltage Category	III
Pollution Degree	3
Housing Material	Insulation Group I, RAL 7035
Actuator Material	Insulation Group II, Black, Sealable
Actuator Marking	I / O
Contact Position Indication	Red ON / Green OFF
Degree of Protection	IP20
Remarks	IP40 in enclosure with cover 20000 cycle
Terminal Type	Screw Terminals
Screw Terminal Type	Failsafe Bi-directional Cylinder-lift Terminal
Connecting Capacity	Busbar 10 / 10 mm <sup>2</sup> Flexible with Ferrule 0.75 ... 25 mm <sup>2</sup> Flexible 0.75 ... 25 mm <sup>2</sup> Rigid 0.75 ... 35 mm <sup>2</sup> Stranded 0.75 ... 35 mm <sup>2</sup>
Tightening Torque	2.8 N·m
Recommended Screw Driver	Pozidriv 2
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Position	Any
Built-In Depth ( $t_2$ )	69 mm
Installation Size	acc. to DIN 43880 3
Power Supply Connection	Arbitrary

## Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
Resistance to Shock acc. to IEC 60068-2-27	25g / 2 shocks / 13 ms
Resistance to Vibrations acc. to IEC 60068-2-6	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	480Y / 277 V AC 96 V DC
Connecting Capacity UL/CSA	Busbar 18-8 AWG Conductor 18-4 AWG
Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA

## Dimensions

Product Net Width	35 mm
Product Net Depth / Length	69 mm
Product Net Height	111 mm

Product Net Weight	0.25 kg
--------------------	---------

---

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	40 mm
Package Level 1 Depth / Length	120 mm
Package Level 1 Height	83 mm
Package Level 1 Gross Weight	0.27 kg
Package Level 1 EAN	4016779931045
Package Level 2 Units	36 piece
Package Level 2 Width	275 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Height	210 mm
Package Level 2 Gross Weight	16 kg
Package Level 2 EAN	4016779938587

---

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85362010

---

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CDK400595D2704
Instructions and Manuals	2CDC002177D0202
RoHS Information	2CDK400595D2704

---

### Popular Downloads

Data Sheet, Technical Information	2CDC002177D0202
Instructions and Manuals	2CDC002177D0202

---

### Classifications

ETIM 6	EC000042 - Miniature circuit breaker (MCB)
ETIM 7	EC000042 - Miniature circuit breaker (MCB)
eClass	7.0 27141901
UNSPSC	39121614

---

### Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs

