

## Replacement die - CRIMPFOX-M 10/DIE - 1212080

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for ferrules 0.25 - 10 mm<sup>2</sup>, packed in a serial storage box

### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356454506
Weight per Piece (excluding packing)	88.000 g
Custom tariff number	82032000
Country of origin	Sweden
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	114 mm
Width (a)	75 mm
Height (c)	25.5 mm

#### General

Color	black
Compression	Trapezoidal crimp
Type of contact	Ferrules
Designation	Crimping position 1
Min. cross section	0.25 mm <sup>2</sup>
Max. cross section	0.75 mm <sup>2</sup>
AWG min	24
AWG max	20
Designation	Crimping position 2
Min. cross section	1 mm <sup>2</sup>
Max. cross section	1.5 mm <sup>2</sup>
AWG min	18
AWG max	16

# Replacement die - CRIMPFOX-M 10/DIE - 1212080

## Technical data

### General

Designation	Crimping position 3
Max. cross section	2.5 mm <sup>2</sup>
AWG max	14
Die station	Crimping position 4
Max. cross section	4 mm <sup>2</sup>
AWG max	12
Die station	Crimping position 5
Max. cross section	10 mm <sup>2</sup>
AWG max	10
Weight	86 g
Min. cross section	0.25 mm <sup>2</sup>
Max. cross section	10 mm <sup>2</sup>

## Classifications

### eCl@ss

eCl@ss 10.0.1	21019290
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

## Replacement die - CRIMPFOX-M 10/DIE - 1212080

### Approvals

Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

---