

Cable-cutting tool - CUTFOX-S VDE_DB - 1212790

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested, type of packaging: with holder for sales display (backcard)

Your advantages

- Inductively hardened blades for long-term stable cutting performance
- VDE-tested cutting tools made from special high-grade tool steel

Key Commercial Data

| | |
|--------------------------------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4046356994668 |
| Weight per Piece (excluding packing) | 227.900 g |
| Custom tariff number | 82032000 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|----------------|------------------|
| Length (b) | 160 mm |
| Cable diameter | 0.2 mm ... 11 mm |

General

| | |
|--------------------|----------------------------------|
| Test standard | DIN EN 60900 (VDE 0682 PART 201) |
| | DIN ISO 5746 |
| Weight | 230 g |
| Min. cross section | 0 mm ² |

Standards and Regulations

| | |
|---------------|----------------------------------|
| Test standard | DIN EN 60900 (VDE 0682 PART 201) |
| | DIN ISO 5746 |

Environmental Product Compliance

| | |
|---------------------------|---------------------------------------------------------------------------------------------------------------|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---------------------------------------------------------------------------------------------------------------|

Cable-cutting tool - CUTFOX-S VDE_DB - 1212790

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 21043711 |
| eCl@ss 4.0 | 21040300 |
| eCl@ss 4.1 | 21040300 |
| eCl@ss 5.0 | 21040300 |
| eCl@ss 5.1 | 21040300 |
| eCl@ss 6.0 | 21043700 |
| eCl@ss 7.0 | 21043711 |
| eCl@ss 8.0 | 21043711 |
| eCl@ss 9.0 | 21043711 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000142 |
| ETIM 3.0 | EC000142 |
| ETIM 4.0 | EC000142 |
| ETIM 5.0 | EC000142 |
| ETIM 6.0 | EC000165 |
| ETIM 7.0 | EC000165 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 23171604 |
| UNSPSC 7.0901 | 23171604 |
| UNSPSC 11 | 23171604 |
| UNSPSC 12.01 | 23171604 |
| UNSPSC 13.2 | 27111506 |
| UNSPSC 18.0 | 27111511 |
| UNSPSC 19.0 | 27111511 |
| UNSPSC 20.0 | 27111511 |
| UNSPSC 21.0 | 27111511 |

Approvals

Approvals

Approvals


VDE Zeichengenehmigung / EAC

Ex Approvals

Approval details

Cable-cutting tool - CUTFOX-S VDE_DB - 1212790

Approvals

| | | | |
|------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|
| VDE Zeichengenehmigung |  | http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx | 109845 |
|------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|

| | | | |
|-----|-----------------------------------------------------------------------------------|--|--------------------------|
| EAC |  | | RU x- DE.xx08.B.02974 |
|-----|-----------------------------------------------------------------------------------|--|--------------------------|