

## USB-C to DVI Adapter with PD Charging, Black

MODEL NUMBER: **U444-06N-DB-C**



USB-C adapter adds DVI and USB-C PD ports to your laptop, MacBook, Chromebook or other compatible device.

### Features

**USB to DVI Adapter Connects to Your Device's USB-C or Thunderbolt 3 Port**This USB-C adapter helps you transmit video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a DVI-enabled television, monitor or projector. It's ideal for transmitting 1080p video to a large display, as well as powering and charging a PD Charging-compliant mobile device.

**Supports USB DisplayPort Alternate Mode for Transmitting Video Signals**With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

**Transmits Crystal-Clear 1080p Video to a DVI Display**To send high-definition video to a DVI television, projector or monitor, connect the DVI port to the display using a DVI cable (sold separately). The DVI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

**Charges the Connected Laptop, Smartphone or Other Device**The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the adapter is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W.

**Built-In USB-C Cable Connects in Either Direction**Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

**Ready to Use Right Out of the Package**The plug-and-play USB to DVI adapter requires no software, drivers or external power. It's smaller than a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

**3-Year Warranty**The U444-06N-DB-C is backed by a 3-year warranty, ensuring reliability and performance.

### Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- USB-C PD charging port supports power input up to 20V 3A (60W)
- Easy installation with plug-and-play operation—no software required

### Applications

- Play 1080p video from your laptop or PC on a DVI display
- Give a video presentation at a meeting, training session or conference
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Multitask in two or more applications on multiple displays
- Add a second monitor and make it your primary monitor
- Edit large documents on two different monitors

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI input



(DVI port)

**Package Includes**

- U444-06N-DB-C USB-C to DVI Adapter w/PD Charging - USB 3.1, Thunderbolt 3, 1080p, Black
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332210715
OUTPUT	
Charging Ports / Amps	3A / 2A / 1.5A
Charging Watts	60
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (1.2 Port)	No
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	PVC and ABS
Shipping Dimensions (hwd / cm)	2.01 x 11.68 x 9.91
Shipping Dimensions (hwd / in.)	0.79 x 4.60 x 3.90
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.55 x 2.3 x 1.6
Unit Packaging Type	Box



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.07
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	2.1 BTU/Hr
Power Consumption (Watts)	0.6
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C)
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	USB Type-C (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	DVI: 1920 X 1080 (1080P) @ 60HZ
Displayport Specification	1.2
HDCP Specification	1.2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
USB Power Delivery (PD) Charging Support	Yes
Technology	USB 3.1 (Gen 1); DVI; USB; PD Charging
USB Power Delivery (PD) Charging Specification	2.0
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>