

Cable marker - LS-WMTB-V4A (60X15) CUS - 0831804

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker, can be ordered: Piece, silver, labeled according to customer specifications, mounting type: Assembly with cable binders, cable diameter: > 4.6 mm, lettering field size: 60 x 15 mm, Number of individual labels: 16



Your advantages

- Stainless steel cable marking for assembly with cable binders
- High-quality appearance
- Suitable for large-surface marking of conductors and cables > 4.6 mm in diameter

Key Commercial Data

| | |
|--------------------------------------|--------------------------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4046356930130 |
| Weight per Piece (excluding packing) | 83.400 g |
| Custom tariff number | 83100000 |
| Country of origin | Poland |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------------------|---------|
| Length (b) | 78 mm |
| Width (a) | 15 mm |
| Material thickness (g) | 0.50 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -80 °C ... 400 °C |
|---------------------------------|-------------------|

General

| | |
|-------|-----------|
| Color | silver |
| Type | Card form |

Cable marker - LS-WMTB-V4A (60X15) CUS - 0831804

Technical data

General

| | |
|---|--|
| Components | free from silicone, halogen, and cadmium |
| Material | V4A |
| RoHS compliant | Yes |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 16 |
| Printability | Direct laser marking |
| Device | 0831831 TOPMARK LASER |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Result of weather resistance test | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Alternating condensation climate with SO2 test specification | following DIN 50018:2013-05 |
| Climate level | AHT 1.0 S |
| Cycles | 2 |
| Condensation test result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test | Test passed |
| Marking mounting type | Assembly with cable binders |

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27400400 |
| eCl@ss 5.1 | 27400400 |
| eCl@ss 6.0 | 27400400 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001530 |

Cable marker - LS-WMTB-V4A (60X15) CUS - 0831804

Classifications

ETIM

| | |
|----------|----------|
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |