

## Cable marker - US-WMT (23X4) CUS - 0829985

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker, can be ordered: By card, white, labeled according to customer specifications, mounting type: thread on, cable diameter range: 1.5 ... 35 mm, lettering field size: 23 x 4 mm, Number of individual labels: 56




### Your advantages

- The US-WMT ... UniSheet labeling range includes markers for conductor marking with marking collars from the PATG/PATO ... system
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements



### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| GTIN                                 | <br>4 046356 613095 |
| GTIN                                 | 4046356613095   |
| Weight per Piece (excluding packing) | 11.080 g  |
| Custom tariff number                 | 49119900  |
| Country of origin                    | Poland  |
| Note                                 | Made to Order (non-returnable)  |

### Technical data

#### Dimensions

|                |                  |
|----------------|------------------|
| Length (b)     | 4.3 mm           |
| Width (a)      | 23 mm            |
| Cable diameter | 1.5 mm ... 35 mm |

#### Ambient conditions

|                                 |   |
|---------------------------------|---|
| Ambient temperature (operation) | -30 °C ... 80 °C  |
| Recommended storage conditions  | 10-30 °C / 40-70 % relative humidity. Storage in the original packaging is recommended prior to processing. |

#### General

|            |               |
|------------|---------------|
| Color      | white         |
| Components | Silicone-free |

# Cable marker - US-WMT (23X4) CUS - 0829985

## Technical data

### General

|   |                                     |
|---|-------------------------------------|
| Flammability rating according to UL 94                              | V0                                  |
| Material  | PVC                                 |
| Wipe resistance   | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels   | 56                                  |
| Number of individual labels per row                                 | 14                                  |
| Printability  | Thermal transfer                    |
| Device  | 5146464 THERMOMARK CARD             |
| Ink ribbon  | 5146451 THERMOMARK CARD-US-MAG1     |
|   | 0801371 THERMOMARK-RIBBON 110-TC    |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result  | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration   | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration   | 96 h                                |
| Salt spray testing result   | Test passed                         |
| Alternating condensation climate with SO2 test specification        | following DIN 50018:2013-05         |
| Climate level   | AHT 1.0 S                           |
| Cycles  | 2                                   |
| Condensation test result  | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Marking mounting type   | thread on                           |

### Standards and Regulations

|  |                             |
|--|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V0                          |

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 27061700 |
| eCl@ss 4.1    | 27061700 |
| eCl@ss 5.0    | 27400400 |
| eCl@ss 5.1    | 27400400 |
| eCl@ss 6.0    | 27400400 |
| eCl@ss 7.0    | 27400401 |
| eCl@ss 8.0    | 27400401 |
| eCl@ss 9.0    | 27400629 |

## Cable marker - US-WMT (23X4) CUS - 0829985

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001530 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |