




## Main

|                              |                                                      |
|------------------------------|------------------------------------------------------|
| Range                        | TeSys                                                |
| Product or component type    | Specific contactor coil                              |
| Device short name            | LX9FF                                                |
| Range compatibility          | TeSys F LC1F contactor                               |
| Product compatibility        | LC1F150<br>LC1F115                                   |
| Control circuit type         | AC at 40...400 Hz low consumption                    |
| [Uc] control circuit voltage | 380...400 V AC 40...400 Hz                           |
| Average resistance           | 173 Ohm inrush at 20 °C<br>6540 Ohm holding at 20 °C |
| Inductance of closed circuit | 23 H                                                 |
| Operating time               | 130 ms opening<br>35 ms closing                      |
| Mechanical durability        | 10 Mcycles                                           |
| Maximum operating rate       | 2400 cyc/h 55 °C                                     |

## Complementary

|                                 |                                                                              |
|---------------------------------|------------------------------------------------------------------------------|
| Coil technology                 | Without built-in suppressor module                                           |
| Control circuit voltage limits  | Operational: 0.85...1.1 Uc (at 55 °C)<br>Drop-out: 0.35...0.55 Uc (at 55 °C) |
| Inrush power in VA              | 690...855 VA 40...400 Hz (at 20 °C)                                          |
| Hold-in power consumption in VA | 6.6...8.1 VA 40...400 Hz (at 20 °C)                                          |
| Heat dissipation                | 5.9...7.2 W                                                                  |

## Environment

|                                       |            |
|---------------------------------------|------------|
| Ambient air temperature for operation | -5...55 °C |
| Net weight                            | 0.43 kg    |

## Offer Sustainability

|                            |                                                                                                   |
|----------------------------|---------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                             |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                 |
| REACH free of SVHC         | Yes                                                                                               |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes                                                                                               |
| RoHS exemption information | <a href="#">Yes</a>                                                                               |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>                                                            |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                     |
| Circularity Profile        | <a href="#">End of Life Information</a>                                                           |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|