



PRODUCT-DETAILS

EPB25-308 CD-UK

EPB25-308CD-UK-(width470mm)

General Information

Extended Product Type	EPB25-308 CD-UK
Product ID	1SKP808142C9751
EAN	6221115051860
Catalog Description	EPB25-308CD-UK-(width470mm)
Long Description	3 -phase protecta busbar type 8 way, surface, 250A, including Isolator kit EPB KIT 8C, with overall depth 160mm, and width 470 mm. (UK)

Ordering

EAN	6221115051860
Minimum Order Quantity	1 piece
Customs Tariff Number	85389738

Dimensions

Product Net Width	470 mm
Product Net Height	610 mm
Product Net Depth / Length	160 mm

Additional Information

Color	Grey
Cover Plate Type	Door
Degree of Protection	IP41
Housing Material	Steel
Mounting Type	Surface mounted (plaster)
Product Name	Sub Distribution
Protection Class	Grounded
Rated Current (I _n)	250 A
Surface Finishing	Powder coating

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SKC802015C0203
Declaration of	1SKC100819C0001

Conformity - CE

Instructions and
Manuals

1SKC802015C0203

Classifications

ETIM 6

EC000058 - Empty cabinet

ETIM 7

EC000058 - Empty cabinet

WEEE Category

Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Enclosures → Sub Distribution Boards → Sub Distribution Boards