

PRODUCT-DETAILS

DSE201 C32 AC30 - N Blue

DSE201 C32 AC30 - N Blue - RCBO



General Information

Extended Product Type	DSE201 C32 AC30 - N Blue
Product ID	2CSR255051R1324
EAN	8012542660026
Catalog Description	DSE201 C32 AC30 - N Blue - RCBO
Long Description	DSE201 is a 1P+N residual current circuit breaker with overcurrent protection (RCBO) in one module for the protection against short-circuit currents, overload, earth fault currents, indirect contacts, additional protection against direct contacts (30 mA versions). DSE201 is equipped with supply neutral wire and functional earth wire.

Technical

Standards	IEC 61009-1 IEC 61009-2-2 AS/NZS 61009-1
Type of Residual Current	AC type
Number of Poles	1+N
Number of Protected Poles	1
Rated Current (I_n)	32 A
Rated Voltage (U_r)	230-240 V AC
Rated Insulation Voltage (U_i)	500 V

Overvoltage Category	III
Pollution Degree	2
Test Voltage (Ut)	195 ... 264 V
Rated Frequency (f)	50...60 Hz
Rated Short-Circuit Capacity (I _{cn})	(230 / 400 V AC) 6 kA
Rated Residual Breaking Capacity (I _{Δm})	6 kA
Primary Rated Impulse Withstand Voltage	4 kV
Dielectric Test Voltage	2.5 kV
Tripping Characteristic	C
Energy Limiting Class	3
Housing Type	Insulation group II, RAL 7035
Actuator Type	Toggle - Insulation group IIIA, black, sealable in ON-OFF positions
Electrical Endurance	10000 cycle 20000 cycle
Degree of Protection	Housing IP40 Terminals IP20
Resistance to Shock acc. to IEC 60068-2-27	30g / 2 shocks / 13 ms
Resistance to Vibrations acc. to IEC 60068-2-6	0.35mm or 5g - 20 cycles at 5...150...5 Hz without load
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
Reference Ambient Air Temperature	30 °C
Terminal Type	Screw Terminals
Screw Terminal Type	Cage Terminal
Connecting Capacity	Busbar 10 mm ² Rigid 25 ...25 mm ² Flexible 25 ...25 mm ²
Tightening Torque	Top 1.2 N·m Bottom 2.8 N·m
Mounting Type	on DIN rail EN 60715 (35 mm) by means of fast clip device in consumer unit Type A according to IEC 61439-1&3, BS EN 61439-1&3, in distribution board Type B according to IEC 61439-1&3, BS EN 61439-1&3.
Power Supply Connection	Bottom
Position of Neutral Terminals	Right
Power Loss	5.2 W

Environmental

Ambient Air Temperature	Operation -25...55 °C
RoHS Status	Following EU Directive 2011/65/EU

Dimensions

Product Net Width	0.018 m
Product Net Height	0.100 m

Product Net Depth / Length	0.069 m
Product Net Weight	0.180 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.036 m
Package Level 1 Height	0.088 m
Package Level 1 Depth / Length	0.143 m
Package Level 1 Gross Weight	0.200 kg
Package Level 1 EAN	8012542660026
Package Level 2 Units	30 piece
Package Level 2 Width	0.200 m
Package Level 2 Height	0.175 m
Package Level 2 Depth / Length	0.440 m
Package Level 2 Gross Weight	6.975 kg
Package Level 2 EAN	8012542342427

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5595
Environmental Information	refer to RoHS information
Instructions and Manuals	9AKK106930A0912
RoHS Information	2CSC422006K2701

Popular Downloads

Data Sheet, Technical Information	9AKK106930A0940
Instructions and Manuals	9AKK106930A0912

Classifications

Object Classification Code	Q
ETIM 4	EC000905 - Earth leakage circuit breaker
ETIM 5	EC000905 - Earth leakage circuit breaker
ETIM 6	EC000905 - Earth leakage circuit breaker
ETIM 7	EC000905 - Earth leakage circuit breaker

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Circuit Breakers with Overcurrent Protection RCBO

