

LQM2MPN2R2MGH#

indicates a package specification code.



< List of part numbers with package codes >
 LQM2MPN2R2MGHL , LQM2MPN2R2MGHB

Shape

L size	2.0 ± 0.2mm
W size	1.6 ± 0.2mm
T size	0.9 ± 0.1mm
Size code in inch (mm)	0806 (2016)

Notes

When rated current is applied to the products, inductance will be within ±30% of initial inductance value range.
 When rated current is applied to the products, the temperature rise caused by self-generated heat shall be limited to 40 °C max.
 Keep the temperature (ambient temperature plus self-generation of heat) under 125 °C.

References

Packaging code	Specifications	Minimum quantity
L	φ 180mm Embossed taping	3000
B	Packing in bulk	1000





Mass (Typ.)	
1 piece	0.012g

Specifications

Inductance	2.2μH ±20%
Inductance test frequency	1MHz
Rated current (I _{sat}) (Based on Inductance change)	1.3A(Max) / 1.5A(Typ.)
Rated current (I _{temp}) (Based on Temperature rise)	1.0A(Max) / 1.3A(Typ.)
Max. of DC resistance	0.263Ω
Avg. of DC resistance	0.21Ω (typ.)
Self resonance frequency (min.)	40MHz
Operating temperature range	-40°C to 85°C
Class of magnetic shield	Ferrite Core
Series	LQM2MPN_GH

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.