

LQP02HQ0N4C02#

indicates a package specification code.



< List of part numbers with package codes >
 LQP02HQ0N4C02E , LQP02HQ0N4C02L , LQP02HQ0N4C02B

Shape

L size	0.4 ±0.02mm
W size	0.2 ±0.02mm
T size	0.3 ±0.02mm
Size code in inch (mm)	01005 (0402)

References

Packaging code	Specifications	Minimum quantity
L	φ 180mm Embossed taping	30000
B	Packing in bulk	500
E	φ 180mm Embossed taping (W8P2*) *Width : 8mm, Pocket pitch : 2mm	15000




Mass (Typ.)	
1 piece	0.000085g

Specifications

Inductance	0.4nH ±0.2nH
Inductance test frequency	500MHz
Rated current (Itemp) (Based on Temperature rise)	1000mA
Max. of DC resistance	0.03Ω
Q (min.)	14
Q test frequency	500MHz
Self resonance frequency (min.)	17.0GHz
Operating temperature range (Self-temperature rise is not included)	-55°C to 125°C
Series	LQP02HQ_02

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.