


**LPH350****112-00401**

LPH175 Series



These cable ties are "outside serrated", presenting a smooth surface to the cable bundle and avoiding any problems with damage to the insulation, the width of the ties gives a broad contact area with the cable, again minimising the risk of damage. The PE/RPE ranges have the benefit of EDF (French Electricity Board) approval. The "Low Profile" design of the head allows for use in applications with restricted space. The RP ties are releasable and reusable allowing for the addition or removal of cables after installation.

Designed primarily for use within the electrical supply industry these ties are particularly useful in areas with limited space, e.g.cable bundling in shafts and are particularly suitable for outdoor use as they are manufactured from "UV" resistant polyamides.

**Base Data****Colour**

Black (BK)

**Package Content**

100

**Quantity per**

Bag

**Recommended Application Tool**

MK6, MK9P, MK6PN, MK9, MK9HT, MK21

**Logisitic and Packaging****EAN code**

5016371006225

**Material and Specifications****Flammability**

UL94 V2

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Operating Temperature (Metric)**

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

**Product Dimensions****Bundle Diameter max (Metric)**

92

**Bundle Diameter min (Metric)**

25

**Length L (Metric)**

355

**Minimum Tensile Strength (N)**

480

**Width W (Metric)**

9