

# RP73D1J1K91BTG ✓ ACTIVE

Holsworthy | Holsworthy RP73


TE Internal #: 5-1879745-3

Holsworthy RP73, Surface Mount Resistors, Precision Resistor, 2 Terminations, Size Code 0603, Cut Tape Length, .1%, Thin Film

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Size Code: **0603**

Packaging Method: **Cut Tape Length**

Tolerance: **.1%**

## Features

### Product Type Features

Product Type	Fixed Resistor
Resistor Type	Precision Resistor
Size Code	0603
Element Type	Thin Film

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Voltage Rating	75 V
Tolerance	.1%
Resistance Range	1k $\Omega$ – 1M $\Omega$
Resistance	1.91K $\Omega$
Power Rating	.1 W

### Termination Features

Number of Terminations	2
Termination Type	Solder

### Mechanical Attachment

Mount Style	Surface Mount
-------------	---------------

### Dimensions

--	--



Dimensions	1.55 x .8 x .45 mm
------------	--------------------

**Usage Conditions**

Temperature Coefficient	±15 ppm/°C
-------------------------	------------

**Packaging Features**

Packaging Method	Cut Tape Length
------------------	-----------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

**Compatible Parts**




TE Model / Part # 9-1879252-4  
RP 2B 10R 0.1% 15PPM CUT LENGTH



TE Model / Part # 5-1879267-0  
RP 2B 1M0 0.1% 15PPM 1K RL



TE Model / Part # 2-1879747-4  
RP 1J 110K 0.1% 15PPM CUT LENGTH



TE Model / Part # 5-1879743-7  
RP 1J 18R2 0.1% 15PPM CUT LENGTH




TE Model / Part # 2-1879279-6  
RP 2A 75K 0.1% 15PPM 1K RL

Also in the Series | **Holsworthy RP73**



Surface Mount Resistors(2547)

Customers Also Bought



TE Model / Part #1-6437006-1  
609-1603LF = PCB IDC P 16 ST .062



TE Model / Part #4-1879134-9  
RN 0603 31K6 0.1% 10PPM 1K RL



TE Model / Part #1618241-9  
K81A335=RELAY, VACUUM, SPST-NO



TE Model / Part #1622726-1  
LR2 1% 2K4



TE Model / Part #1-825433-5  
MOD 2 PINHDR 1X15P.



TE Model / Part #1676656-1  
RN 0805 16R2 0.1% 10PPM CUT LENGTH



TE Model / Part #5-1879746-4  
RP 1J 21K 0.1% 15PPM CUT LENGTH



## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-1879745-3\\_BA.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-1879745-3\\_BA.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-1879745-3\\_BA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[RP73-0915](#)

English

[8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS\\_FOR\\_ELEVATORS\\_AND\\_ESCALATORS](#)

English