


**T18L****111-02029**

T18S – T250XL



Available in a wide range of materials, these cable ties all feature internal serrations allowing for a positive hold onto cable, hose and pipe bundles. The design of the head guarantees a high tensile strength whilst allowing a very low insertion force, this, combined with the bent tail design of many of the ties, ensures a simple and quick installation. Whilst easily installed by hand, manual and pneumatic (for high volume applications) tensioning tools are available to ensure a consistent and safe installation.

For the routing, bundling and securing of cables, pipes and hoses.

**Base Data****Application Method**

Quick, simple fixing by hand or with HellermannTyton tensioning tools

**Colour**

Natural (NA)

**Label E-Number Finland**

13 707 56

**Label E-Number Sweden**

15 160 12

**Package Content**

1000

**Quantity (Sold Unit / EDP)**

1000

**Quantity per**

Bag

**Recommended Application Tool**

MK3SP, MK3PNSP2, MK7P, MK7, MK20

**Logistic and Packaging****Carton Quantity**

20000

**EAN code**

4031026104379

**Quantity of Europallet**

360000

**Weight (kg) (Metric)**

0.3 kg

**Material and Specifications****Flammability**

UL94 V2

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Operating Temperature (Metric)**

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

**Product Dimensions****Bundle Diameter max (Imperial)**

2.17 "

**Bundle Diameter max (Metric)**

55

**Bundle Diameter min (Imperial)**

.06 "

**Bundle Diameter min (Metric)**

1.5

**Length L (Imperial)**

8.0 "

**Length L (Metric)**

205 mm

**Minimum Tensile Strength (imperial)**

18

**Minimum Tensile Strength (N)**

80

**Width W (Imperial)**

.10 "

**Width W (Metric)**

2.5

© HellermannTyton 2006