



### Main

|                           |                                                                            |
|---------------------------|----------------------------------------------------------------------------|
| Range of product          | TeSys                                                                      |
| Range                     | TeSys                                                                      |
| Device short name         | DE1D                                                                       |
| Product or component type | Enclosure                                                                  |
| Material                  | Polycarbonate                                                              |
| Device composition        | Contacteur ordered separately<br>Thermal overload relay ordered separately |
| Product compatibility     | LE1D18...35                                                                |
| Control type              | Without                                                                    |

### Complementary

|                    |                                                                                                    |
|--------------------|----------------------------------------------------------------------------------------------------|
| Cable entry number | 2 ISO20 top<br>2 ISO20 bottom<br>2 Pg 16 bottom<br>2 ISO25 top<br>2 Pg 21 bottom<br>2 ISO25 bottom |
| Height             | 201 mm                                                                                             |
| Width              | 103 mm                                                                                             |
| Depth              | 145 mm                                                                                             |
| Net weight         | 0.5 kg                                                                                             |

### Environment

|                                       |                              |
|---------------------------------------|------------------------------|
| IP degree of protection               | IP65 conforming to IEC 60529 |
| IK degree of protection               | IK07 conforming to IEC 60529 |
| Ambient air temperature for operation | -5...40 °C                   |
| Environmental characteristic          | Standard environment         |

**Offer Sustainability**

|                            |                                                  |
|----------------------------|--------------------------------------------------|
| Sustainable offer status   | Green Premium product                            |
| REACH free of SVHC         | Yes                                              |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                              |
| Mercury free               | Yes                                              |
| RoHS exemption information | <a href="#">Yes</a>                              |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>    |

**Contractual warranty**

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|