

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys D
Product or component type	Contactor
Device short name	LC1D
Contactor application	Resistive load Motor control
Utilisation category	AC-1 AC-4 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	Power circuit <= 1000 V AC 25...400 Hz Power circuit <= 300 V DC
[Ie] rated operational current	200 A 140 °F (60 °C) <= 440 V AC AC-1 power circuit 115 A 140 °F (60 °C) <= 440 V AC AC-3 power circuit
Motor power kW	30 kW 220...230 V AC 50/60 Hz AC-3) 55 kW 380...400 V AC 50/60 Hz AC-3) 59 kW 415...440 V AC 50/60 Hz AC-3) 75 kW 500 V AC 50/60 Hz AC-3) 80 kW 660...690 V AC 50/60 Hz AC-3) 65 kW 1000 V AC 50/60 Hz AC-3) 18.5 kW 400 V AC 50/60 Hz AC-4)
Motor power HP (UL / CSA)	30 hp 200/208 V AC 50/60 Hz 3 phase 40 hp 230/240 V AC 50/60 Hz 3 phase 75 hp 460/480 V AC 50/60 Hz 3 phase 100 hp 575/600 V AC 50/60 Hz 3 phase
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	48 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 1 NC
[Uimp] rated impulse withstand voltage	8 kV IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Overvoltage category	III
[I _{th}] conventional free air thermal current	200 A 140 °F (60 °C) power circuit
I _{rms} rated making capacity	1260 A 440 V power circuit IEC 60947 140 A AC signalling circuit IEC 60947-5-1 250 A DC signalling circuit IEC 60947-5-1
Rated breaking capacity	1100 A 440 V power circuit IEC 60947
[I _{cw}] rated short-time withstand current	250 A 104 °F (40 °C) - 10 min power circuit 550 A 104 °F (40 °C) - 1 min power circuit 950 A 104 °F (40 °C) - 10 s power circuit 1100 A 104 °F (40 °C) - 1 s power circuit 100 A - 1 s signalling circuit 120 A - 500 ms signalling circuit 140 A - 100 ms signalling circuit
Associated fuse rating	250 A gG <= 690 V type 1 power circuit 200 A gG <= 690 V type 2 power circuit 10 A gG signalling circuit
Average impedance	0.6 mOhm - I _{th} 200 A 50 Hz power circuit
[U _i] rated insulation voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 1000 V IEC 60947-4-1 Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL
Electrical durability	0.8 Mcycles 200 A AC-1 <= 440 V 0.95 Mcycles 115 A AC-3 <= 440 V
Power dissipation per pole	24 W AC-1 7.9 W AC-3
Safety cover	With
Mounting support	Rail Plate
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	LROS (Lloyds register of shipping) GL CSA BV GOST CCC DNV UL RINA
Connections - terminals	Control circuit lugs-ring terminals 0.31 in (8 mm)) Power circuit lugs-ring terminals 0.98 in (25 mm)) Power circuit bars 1 5 x 25 mm
Tightening torque	Control circuit 10.62 lbf.in (1.2 N.m) lugs-ring terminals flat Ø 6 mm M3.5 Control circuit 10.62 lbf.in (1.2 N.m) lugs-ring terminals Philips No 2 M3.5 Power circuit 106.21 lbf.in (12 N.m) lugs-ring terminals hexagonal 0.51 in (13 mm) M8 Power circuit 106.21 lbf.in (12 N.m) bars hexagonal 0.51 in (13 mm) M8
Operating time	6...20 ms opening 20...50 ms closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	8 Mcycles
Maximum operating rate	2400 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Built-in bidirectional peak limiting diode suppressor
Control circuit voltage limits	Drop-out 0.3...0.5 U _c AC 50/60 Hz 131 °F (55 °C)) Operational 0.8...1.15 U _c AC 50/60 Hz 131 °F (55 °C))
Inrush power in VA	280...350 VA 60 Hz 0.8 68 °F (20 °C))

	280...350 VA 50 Hz 0.8 68 °F (20 °C))
Hold-in power consumption in VA	2...18 VA 60 Hz 0.3 68 °F (20 °C)) 2...18 VA 50 Hz 0.3 68 °F (20 °C))
Heat dissipation	3...8 W 50/60 Hz
Auxiliary contacts type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA signalling circuit
Minimum switching voltage	17 V signalling circuit
Non-overlap time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation resistance	> 10 MOhm signalling circuit

Environment

IP degree of protection	IP20 front face IEC 60529
Protective treatment	TH IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C) at Uc
Operating altitude	9842.52 ft (3000 m) without
Fire resistance	1562 °F (850 °C) IEC 60695-2-1
Flame retardance	V1 UL 94
Mechanical robustness	Vibrations contactor open2 Gn, 5...300 Hz Vibrations contactor closed4 Gn, 5...300 Hz Shocks contactor closed15 Gn for 11 ms Shocks contactor open6 Gn for 11 ms
Height	6.22 in (158 mm)
Width	4.72 in (120 mm)
Depth	5.35 in (136 mm)
Net weight	5.51 lb(US) (2.5 kg)

Ordering and shipping details

Category	22359 - CTR, TESYS D, OPEN, 80-150A AC&DC
Discount Schedule	I12
GTIN	00785901012719
Returnability	No
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
------	--

Contractual warranty

Warranty	18 months
----------	-----------
