



### Main

Range	TeSys
Product name	TeSys T
Device short name	LTME
Product or component type	Extension module
Device application	Equipment monitoring and control
Range compatibility	TeSys T LTMR motor controller
Supply	Via the controller

### Complementary

[Ui] rated insulation voltage	690 V conforming to EN/IEC 60947-1 690 V conforming to CSA C22.2 No 14 690 V conforming to UL 508
[Uimp] rated impulse withstand voltage	6 kV current or voltage measurement circuit conforming to EN/IEC 60947-4-1 0.8 kV supply, inputs and outputs conforming to EN/IEC 60947-4-1
Logic input number	4
Input current	7 mA
Current state 0 guaranteed	Logic input: < 5 V and <= 15 mA for 5 ms
Current state 1 guaranteed	Logic input: < 15 V and 2...15 mA for 15 ms
Maximum output switching frequency	2 Hz
Maximum operating rate	1800 cyc/h
Contacts type and composition	Without
Metering type	Voltage U21, U32, U13, V1, V2, V3 Imbalance voltage Frequency Calculated active and reactive energy (+/- W.h, +/- VAR.h) Reactive power Q, Q1, Q2, Q3 Power factor Active power P, P1, P2, P3
Measurement accuracy	1 % voltage (100...830 V) 3 % power factor 5 % active and reactive power

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Overvoltage category	III
Connection pitch	5.08 mm
Connections - terminals	Control circuit: connector 1 cable(s) 0.25...2.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible with cable end Control circuit: connector 1 cable(s) 0.2...2.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 1 cable(s) 0.25...2.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 1 cable(s) 0.2...2.5 mm <sup>2</sup> (AWG 24...AWG 14) solid without cable end Control circuit: connector 2 cable(s) 0.2...1 mm <sup>2</sup> (AWG 24...AWG 14) flexible with cable end Control circuit: connector 2 cable(s) 0.2...1.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 2 cable(s) 0.5...1.5 mm <sup>2</sup> (AWG 24...AWG 14) flexible without cable end Control circuit: connector 2 cable(s) 0.2...1 mm <sup>2</sup> (AWG 24...AWG 14) solid without cable end
Tightening torque	Control circuit: 0.5...0.6 N.m flat screwdriver 3 mm
Pollution degree	3
Electromagnetic compatibility	Electrostatic discharge, 3, 8 kV air, 6 kV contact, conforming to EN/IEC 61000-4-2 Fast transients immunity test (other circuits), level 3, 2 kV, conforming to EN/IEC 61000-4-4 Fast transients immunity test (on supply and relay outputs), level 4, 4 kV, conforming to EN/IEC 61000-4-4 Conducted RF disturbances, 10 V, conforming to EN/IEC 61000-4-6 Control circuit: surges (common mode), 1 kV, conforming to EN/IEC 61000-4-5 Control circuit: surges (serial mode), 1 kV, conforming to EN/IEC 61000-4-5 Communication: surges (common mode), 2 kV, conforming to EN/IEC 61000-4-5 Voltage inputs: surges (serial mode), 2 kV, conforming to EN/IEC 61000-4-5 Voltage inputs: surges (common mode), 4 kV, conforming to EN/IEC 61000-4-5
Width	45 mm
Height	61 mm
Depth	120.7 mm
Net weight	0.21 kg
Compatibility code	LTME

## Environment

Standards	IEC 60947-4-1 UL 508 EN 60947-4-1 IACS E10 CSA C22.2 No 14
Product certifications	UL NOM ATEX BV CSA EAC RINA LROS (Lloyds register of shipping) DNV ABS GL KERI RMRoS C-Tick CCC
IP degree of protection	IP20
Protective treatment	12 x 24 hour cycles conforming to EN/IEC 60068-2-30 48 h conforming to EN/IEC 60070-2-11 TH conforming to EN/IEC 60068
Fire resistance	650 °C conforming to EN/IEC 60695-2-12 960 °C conforming to UL 94
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C
Operating altitude	<= 2000 m without derating
Mechanical robustness	Shocks half sine wave acceleration: 15 Gn for 11 ms conforming to EN/IEC 60068-2-27 Vibrations mounted on symmetrical rail: 1 Gn, 5...300 Hz conforming to EN/IEC 60068-2-6 Vibrations plate mounted: 4 Gn, 5...300 Hz conforming to EN/IEC 60068-2-6

## Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------