

ML10/13.SF



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	ML10/13.SF
Product ID:	1SNA199095R1300
EAN:	3472591990959
Catalog Description:	ML10/13.SF Screw Clamp Terminal Blocks - For 6.3 x 25 and 6.3 x 32 fuses - Black
Long Description:	Protect your circuits with 6.35x25.4 and 6.35x32 fuse terminal blocks (fuse not supplied with terminal blocks).

Ordering

Color:	Black
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85361050

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	13 mm
Product Net Height:	85 mm
Product Net Depth / Length:	58 mm
Product Net Weight:	51 g

Technical

Rated Cross-Section:	10 mm ²
Spacing:	13 mm
Connection Type:	Screw clamp
Function:	Fuse
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 ... 10 mm ² Screw Clamp / Rigid 1x 0.5 ... 16 mm ²
Gauge Type:	A6
Rated Current (I_n):	Main Circuit 16 A
Rated Voltage (U_r):	800 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V

Pollution Degree:	3
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	12.0 mm
Recommended Screw Driver:	5.5 mm
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 10 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22 ... 10 AWG Stranded 10 AWG
Flammability According to UL94:	V0

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161066A0201
cUL Certificate:	1SND161000A0203
Declaration of Conformity - CE:	1SND225016U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220021E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101
RoHS Information:	1SND230023F0208

Classifications

Object Classification Code:	X
ETIM 4:	EC000899 - Fuse terminal block
ETIM 5:	EC000899 - Fuse terminal block
ETIM 6:	EC000899 - Fuse terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	172 mm
Package Level 1 Depth / Length:	155 mm

Package Level 1 Height:	71 mm
Package Level 1 Gross Weight:	1.02 kg
Package Level 1 EAN:	3472591990959
Package Level 2 Units:	200 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	300 mm
Package Level 2 Gross Weight:	10.700 kg
Package Level 3 Units:	4800 piece
Product Packing Type:	Box

