

PRODUCT-DETAILS

AF75-40-00 100-250V 50Hz / 100-250V 60Hz /
100-250V DC

AF75-40-00 100-250V 50Hz / 100-250V 60Hz /
100-250V DC Contactor



General Information

Extended Product Type	AF75-40-00 100-250V 50Hz / 100-250V 60Hz / 100-250V DC
Product ID	1SBL417201R7000
EAN	3471522115300
Catalog Description	AF75-40-00 100-250V 50Hz / 100-250V 60Hz / 100-250V DC Contactor

Long Description

AF75 4-pole contactors are mainly used for controlling non-inductive or slightly inductive loads (i.e. resistance furnaces...) and generally for controlling power circuits up to 690 V AC and 440 V DC. The contactors can also be used for many other applications such lighting... The AF... contactors are fitted with an electronic coil interface which accepts a wide control voltage range, on AC 50/60 Hz or DC supplies. The same contactor can accept various supply voltages according to the different countries where the electrical equipment will be installed, or some fluctuation in the control voltage due to the local supply or network. The AF... contactors are also fully suitable for operation in AC or DC control circuit liable to voltage interruptions or voltage dip risks. Advantages: - Wide voltage range, e.g. 100 ... 250 V AC and DC - Can manage large voltage variations - Reduced power consumption - Very distinct closing and opening - Noise free - Can withstand voltage interruptions or voltage dips in the control supply (≤ 20 ms). The AF... series 4-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 4 N.O. main poles, front and side-mounted add-on auxiliary contact blocks - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available.

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching

ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	142 mm
Package Level 1 Depth / Length	190 mm
Package Level 1 Height	136 mm
Package Level 1 Gross Weight	1.42 kg
Package Level 1 EAN	3471522115300
Package Level 2 Units	box 8 piece
Package Level 2 Width	503 mm
Package Level 2 Depth / Length	153 mm
Package Level 2 Height	307 mm
Package Level 2 Gross Weight	11.36 kg
Package Level 3 Units	84 piece

Certificates and Declarations (Document Number)

CB Certificate	CB_CN45489
CCC Certificate	CCC_2018010304134049
CSA Certificate	CSA_1033838_LR056745
Declaration of Conformity - CE	1SBD250803U1000
Environmental Information	1SBD250022E1002
GOST Certificate	GOST_POCCFRME77B07175
Instructions and Manuals	FPTC407734P0003
RoHS Information	1SBD250803U1000
UL Certificate	UL_20120830-E312527-10-1
UL Listing Card	UL_E312527

Environmental

Ambient Air Temperature	Close to Contactor for Storage -60 ... +80 °C Near Contactor for Operation in Free Air -40 ... +70 °C
Maximum Operating Altitude Permissible	3000 m
Resistance to Shock acc. to IEC 60068-2-27	Shock Direction: A 20 K40 Shock Direction: B2 15 K40 Shock Direction: C1 20 K40 Shock Direction: C2 20 K40 Closed, Shock Direction: B1 10 K40 Open, Shock Direction: B1 5 K40
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	4
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	0
Rated Operational Voltage	Main Circuit 690 V
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors $q = 40$ °C 125 A
Rated Operational Current AC-1 (I_e)	(690 V) 40 °C 125 A (690 V) 55 °C 105 A (690 V) 70 °C 85 A
Rated Operational Current AC-3 (I_e)	(220 / 230 / 240 V) 55 °C 75 A (380 / 400 V) 55 °C 75 A (415 V) 55 °C 72 A (440 V) 55 °C 70 A (500 V) 55 °C 65 A (690 V) 55 °C 46 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 22 KWT (380 / 400 V) 37 KWT (415 V) 40 KWT (440 V) 40 KWT (500 V) 45 KWT (690 V) 40 KWT
Short-Circuit Protective Devices	gG Type Fuses 160 A
Maximum Breaking Capacity	$\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 440 V 1300 A $\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 690 V 630 A
Maximum Electrical Switching Frequency	AC-1 300 cycles per hour AC-2 / AC-4 150 cycles per hour AC-3 300 cycles per hour
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Maximum Mechanical Switching Frequency	300 cycles per hour
Rated Control Circuit Voltage (U_c)	50 Hz 100 ... 250 V 60 Hz 100 ... 250 V DC Operation 100 ... 250 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 7 2.8 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 7 2.8 V·A Pull-in at Max. Rated Control Circuit Voltage 50 Hz 210 V·A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 210 V·A
Operate Time	Between Coil De-energization and NC Contact Closing 35 ... 115 ms Between Coil De-energization and NO Contact Opening 30 ... 110 ms Between Coil Energization and NO Contact Closing 30 ... 100 ms
Connecting Capacity Main Circuit	Flexible with Cable End 6 ... 16 mm ² Rigid Cable 6 ... 25 mm ²
Connecting Capacity Auxiliary Circuit	Flexible with Cable End 0.75 ... 2.5 mm ² Rigid Cable 1 ... 4 mm ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20
Terminal Type	Screw Terminals

Dimensions

Product Net Width	92 mm
Product Net Depth / Length	119.5 mm
Product Net Height	110 mm
Product Net Weight	1.42 kg

Popular Downloads

Data Sheet, Technical Information	1SNC001003C0202
Instructions and Manuals	FPTC407734P0003

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

