

PRODUCT-DETAILS

T5N 400 PR221DS-LS/I In=400 4p F F

T5N 400 PR221DS-LS/I In=400 4p F F



General Information

Extended Product Type	T5N 400 PR221DS-LS/I In=400 4p F F
Product ID	1SDA054325R1
EAN	8015644554200
Catalog Description	T5N 400 PR221DS-LS/I In=400 4p F F
Long Description	C.BREAKER TMAX T5N 400 FIXED FOUR-POLE WITH FRONT TERMINALS AND SOLID-STATE RELEASE IN AC PR221DS-LS/I R 400

Ordering

E-Number (Sweden)	3180377
EAN	8015644554200
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	186 mm
Product Net Height	205 mm
Product Net Depth / Length	103.5 mm
Product Net Weight	6.071 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	248 mm
Package Level 1 Height	240 mm
Package Level 1 Depth / Length	285 mm
Package Level 1 Gross Weight	6.6 kg
Package Level 1 EAN	8015644554200

Additional Information

Electrical Durability	7000 cycle 60 cycles per hour
Mechanical Durability	20000 cycle 120 cycles per hour
Number of Poles	4
Power Loss	at Rated Operating Conditions per Pole 16,5 W
Product Main Type	SACE Tmax T
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current (I_n)	Main Circuit 400 A
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(220 V AC) 70 kA (230 V AC) 70 kA (380 V AC) 36 kA (400 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 30 kA (500 V AC) 25 kA (690 V AC) 20 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 5 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(220 V AC) 70 kA (230 V AC) 70 kA (380 V AC) 36 kA (400 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 30 kA (500 V AC) 25 kA (690 V AC) 20 kA (250 V DC) 2 Poles in Series 36 kA (500 V DC) 2 Poles in Series 25 kA (750 V DC) 3 Poles in Series 16 kA
Rated Uninterrupted Current (I_u)	400 A
Release Type	EL
Standards	IEC
Sub-type	T5
Suitable For	T5
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Fixed Circuit-Breakers Front
Test Voltage Max (U_{test})	3500 V
Test Voltage at Industrial Frequency for 1 Minute	3500 V

Version

F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210004D0203
Declaration of Conformity - CE	1SDL000165R0005
Environmental Information	1SDL000143R0
Instructions and Manuals	1SDH000437R0001
Instructions and Manuals (Part 2)	ITSCE-RH0100001
RoHS Information	1SDL000200R0001

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

