

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192020049**
Status: **Active**
Overview: [Splices](#)
Description: NylaKrimp Butt Splice for 10-12 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family [Splices](#)
 Series [19202](#)
 Crimp Quality Equipment Yes
 Overview [Splices](#)
 Product Name Butt, NylaKrimp
 UPC 800753048218

Physical

Barrel Type Closed - Brazed
 Color - Resin Yellow
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 2.703/g
 Packaging Type Bag
 Temperature Range - Operating -55° to +105°C
 Wire Insulation Diameter 5.72mm max.
 Wire Size AWG 10, 12
 Wire Size mm² 3.30-5.00

Electrical


Voltage - Maximum 600V

Material Info

Engineering Number CS-N-346

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing 60002-11C



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ECHA_01_2020 (16
 January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[19202 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

| | |
|---|---------------------------|
| PremiumGrade Hand Crimp Tool | 640010100 |
| Hand Crimp Tool | 640010300 |
| Hand Crimp Tool | 640015000 |
| Crimp Head for the AT-200 Pneumatic Hand Tool | 640050100 |
| Crimp Head for the AT-200 Pneumatic Hand Tool | 640050300 |
| Crimp Head for the AT-200 Pneumatic Hand Tool | 640055000 |

This document was generated on 04/14/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION