


Capacitor, tantalum, 220 uF, 10% Tol, 16V@85C, E



**Dimensions (mm)**

**Specifications**

ID	Dimension	Tolerance
L	7.30	+/-0.30
W	4.30	+/-0.30
H	4.10	+/-0.30
K	1.80	nom
F	2.40	+/-0.10
S	1.30	+/-0.30

<b>Application:</b>	Low ESR
<b>Capacitance:</b>	220 uF
<b>Tolerance:</b>	10%
<b>Voltage DC @ 85C:</b>	16V
<b>Voltage DC @ 105C:</b>	13V
<b>Voltage DC @ 125C:</b>	10V
<b>Temperature Range:</b>	-55/+125C
<b>Size Code:</b>	E
<b>Footprint:</b>	7343
<b>Body Type:</b>	Molded Chip
<b>Packaging:</b>	T&R
<b>Package Quantity:</b>	400
<b>Termination Type:</b>	Tin (Pb free)
<b>Leakage Current:</b>	35.2 uA
<b>Dissipation Factor:</b>	10%
<b>ESR:</b>	100 mOhm
<b>Ripple @ 25C:</b>	1.28 A
<b>Ripple @ 85C:</b>	1.152 A
<b>Ripple @ 125C:</b>	0.512 A