

PRODUCT-DETAILS

VBC6-30-01-01

VBC6-30-01-01 Mini Rev.Contactor 24VDC



General Information

Extended Product Type	VBC6-30-01-01
Product ID	GJL1213901R0011
EAN	4013614053689
Catalog Description	VBC6-30-01-01 Mini Rev.Contactor 24VDC

Long Description

The VBC6-30-01 mini reversing contactor is a compact 3 pole contactor with 1 auxiliary contact, screw terminals and normal mechanical interlock. They are ideally suited for applications where reliability is a must and space is at a premium. Mini reversing contactors are used in residential buildings, commercial buildings and industrial applications for the control of three-phase motor loads up to 4 kW (AC-3). Further features are the noiseless and hum-free coil, a switch position indication and the integrated possibility for rail or wall mounting.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080

Popular Downloads

Data Sheet, Technical Information	1SBC100173C0201
Instructions and Manuals	2CDC102046M6801

Dimensions

Product Net Width	96.5 mm
Product Net Height	57.5 mm
Product Net Depth / Length	46.5 mm
Product Net Weight	0.355 kg

Technical

Number of Poles	4
Rated Operational Voltage	Main Circuit 690 V AC
Rated Frequency (f)	Control Circuit DC Main Circuit 60 Hz Main Circuit 50 Hz Main Circuit DC
Rated Impulse Withstand Voltage (U_{imp})	Main Circuit 6 kV
Rated Insulation Voltage (U_i)	690 V acc. to UL/CSA 600 V
Number of Main Contacts NC	0
Number of Main Contacts NO	3
Rated Operational Current AC-1 (I_e)	(220 / 240 V) 40 °C 20 A (220 / 240 V) 55 °C 16 A (380 / 440 V) 40 °C 20 A (380 / 440 V) 55 °C 16 A (690 V) 40 °C 6 A (690 V) 55 °C 6 A
Rated Operational Power AC-3 (P_e)	4 kW (220 / 230 / 240 V) 2.2 kW (400 V) 4 kW (440 V) 4 kW (500 V) 4 kW (690 V) 3 kW
Rated Short-time Withstand Current (I_{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 64 A
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	0
Conventional Free-air Thermal Current (I_{th})	Main Circuit 20 A
Rated Control Circuit Voltage (U_c)	24 V DC
Coil Operating Limits	(acc. to IEC 60947-4-1) for DC supply 0.85 ... 1.1 x U_c (at $\theta \leq 55$ °C)
Degree of Protection	Auxiliary Circuit Terminals IP20 Control Circuit Terminals IP20 Main Circuit Terminals IP20
Pollution Degree	3
Mechanical Durability	10000000 cycle
Minimum Switching	Auxiliary Circuit 17 V

Capacity	Auxiliary Circuit 5 mA
Maximum Electrical Switching Frequency	AC-1 300 cycles per hour AC-15 600 cycles per hour AC-3 600 cycles per hour DC-1 600 cycles per hour DC-13 600 cycles per hour DC-3 600 cycles per hour
Connecting Capacity Main Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm ² Flexible 1/2x 1 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm ² Flexible 1/2x 1 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm ² Flexible 1/2x 1 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Wire Stripping Length	Auxiliary Circuit 9 mm Main Circuit 9 mm
Tightening Torque	Control Circuit 0.8 ... 1.1 N·m Main Circuit 0.8 ... 1.1 N·m
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Power Loss	at Rated Operating Conditions per Pole 2 W
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Full Load Amps Motor Use	(240 V AC) Single Phase 4.9 A (440 ... 480 V AC) Three Phase 4.8 A
Horsepower Rating UL/CSA	(208 V AC) Three Phase 1 Hp (220 ... 240 V AC) Single Phase 0.5 Hp (220 ... 240 V AC) Three Phase 2 Hp (440 ... 480 V AC) Three Phase 3 Hp (550 ... 600 V AC) Three Phase 1 Hp
General Use Rating UL/CSA	(300 V AC) 12 A
Connecting Capacity Main Circuit UL/CSA	Stranded 1/2x 22-10 AWG
Connecting Capacity Auxiliary Circuit UL/CSA	Stranded 1/2x 22-10 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 7 in·lb Control Circuit 7 in·lb Main Circuit 7 in·lb

Environmental

Ambient Air Temperature	Operation -20 ... +55 °C Storage -40 ... +80 °C
Maximum Operating Altitude Permissible	2000 m

Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 5 ... 150 Hz
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

BV Certificate	1SAA920000-0204
CB Certificate	1SAA938000-2002
CCC Certificate	1SAA938001-3805
cUL Certificate	cUL E191658
Declaration of Conformity - CE	1SAD938515-0001
DNV GL Certificate	1SAA938000-0306
EAC Certificate	1SAA920000-2702
Instructions and Manuals	2CDC102046M6801
KC Certificate	1SAA938000-1501
LR Certificate	1SAA938000-0504
RMRS Certificate	1SAA938000-0704
RoHS Information	1SAD938514-0001

Container Information

Package Level 1 Units	5 piece
Package Level 1 Width	115 mm
Package Level 1 Height	54 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Gross Weight	1.845 kg
Package Level 1 EAN	4013614415746

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000010 - Starter combination
ETIM 6	EC000010 - Combination of contactors
ETIM 7	EC000010 - Combination of contactors
eClass	7.0 27371009
UNSPSC	39121529

Categories

Low Voltage Products and Systems → Control Products → Contactors → Mini Contactors

