


Formable microwave cable SUCOFORM_86_75

Description

Sucoform: Formstable, hand-formable alternatives to semi-rigid microwave cables

75 Ohm, 4 GHz, 165°C, ø2.1 mm, no jacket



Technical Data

Construction

	Material	Detail	Diameter
Centre conductor	Steel, Copper+Silver plated	Wire	0.29 mm
Dielectric	PTFE (Polytetrafluoroethylene)		1.65 mm
Outer conductor	Copper, Tin plated	Tin soaked braid, 100%	2.1 mm

Print: HUBER+SUHNER SUCOFORM 86 75 Ohm (PA no.)

Electrical Data

Impedance	75 Ω +/- 3
Operating Frequency	4 GHz
Capacitance	62 pF/m
Velocity of signal propagation	71 %
Signal delay	4.7 ns/m
Screening effectiveness	≥ 100 dB (up to 4 GHz)
Operating voltage	≤ 1.5 kV _{rms} (at sea level)
Test voltage	3 kV _{rms} (50 Hz/1 min)

Mechanical Data

Weight	1.4 kg/100 m
Min. bending radius	static 6 mm
	repeated (for ≤ 50 bendings) 20 mm

Environmental Data

Temperature range	-65 °C ... +165 °C
Installation temperature	-20 °C... +60 °C
Flame propagation test	IEC 60332-1, UL 1581 § 1080 (VW-1)
Halogen free	No
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
1907/2006/EC (REACH)	compliant
2000/53/EC (ELV)	compliant
2012/19/EU (WEEE)	no special marking needed

Formable microwave cable SUCOFORM_86_75

Additional Information

Ordering Information

Order as SUCOFORM_86_75

Remarks

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Suitable Connectors

Cable group U99 Customer Specific

Formable microwave cable SUCOFORM_86_75

Matrix typical Attenuation [formula: $(a \cdot f^{0.5} + b \cdot f)$] and maximum Power CW [formula: $(p/f^{0.5})$]

Coefficients:

a = 0.671

b = 0.0672

$f_{\max} = 4$

P at 1GHz = 120

Frequency (GHz)	Nom. attenuation (dB / m) sea level 25° C ambient temperature	Nom. attenuation (dB / ft) sea level 25° C ambient temperature	Max. CW power (W) sea level 40° C ambient temperature
0,2	0,31	0,096	268
0,4	0,45	0,138	190
0,6	0,56	0,171	155
0,8	0,65	0,199	134
1,0	0,74	0,225	120
1,2	0,82	0,249	110
1,4	0,89	0,271	101
1,6	0,96	0,291	95
1,8	1,02	0,311	89
2,0	1,08	0,330	85
2,2	1,14	0,348	81
2,4	1,2	0,366	77
2,6	1,26	0,383	74
2,8	1,31	0,400	72
3,0	1,36	0,416	69
3,2	1,42	0,431	67
3,4	1,47	0,447	65
3,6	1,52	0,462	63
3,8	1,56	0,476	62
4,0	1,61	0,491	60