

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail housing, Lower housing part with metal foot catch, with vents, width: 75.9 mm, height: 120.6 mm, depth: 64.3 mm, cross connection: DIN rail connector (optional), number of positions cross connector: 8, color: light gray (7035)

### Your advantages

- Item is from the ME-IO product range
- Tool-free mounting
- Available in overall widths from 75.2 mm
- Inflammability class V0 according to UL 94
- Front push-in connection technology
- Can be mounted on the DIN rail
- Optional with bus connector for DIN rail mounting
- L type



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	
GTIN	4055626199252
Weight per Piece (excluding packing)	69.100 g
Custom tariff number	85472000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Item properties

Brief article description	Mounting base housing
Type	ME-IO 75,2 LB 10U TBUS 7035
Order No.	2202620

# Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

## Technical data

### Item properties

Housing type	DIN rail housing
Type	Lower housing part with metal foot catch
Max. IP code to attain	IP20
Mounting type	DIN rail mounting
Ventilation openings present	yes
Max. number of positions	156 (pitch: 3.45 mm)
	104 (pitch: 5 mm)

### Dimensions

Width [ w ]	75.9 mm
Height [ h ]	120.6 mm
Depth [ d ]	64.3 mm
Depth from top edge of DIN rail [ d ]	57.7 mm

### Material data

Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0
Housing material	Polyamide

### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

### PCB data

Number of PCB holders	4
PCB thickness	1.4 mm ... 1.8 mm
Mounting position	Vertical (horizontal DIN rail)
Type of PCB mount	Latching

### Power dissipation, single housing at 20 °C

Ambient temperature	20 °C
Reduction factor	1
Mounting position	vertical
Power dissipation	8.4 W

### Power dissipation, single housing at 30 °C

Ambient temperature	30 °C
Reduction factor	0.91
Mounting position	vertical
Power dissipation	7.6 W

### Power dissipation, single housing at 40 °C

Ambient temperature	40 °C
---------------------	-------

# Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

## Technical data

### Power dissipation, single housing at 40 °C

Reduction factor	0.81
Mounting position	vertical
Power dissipation	6.8 W

### Power dissipation, single housing at 50 °C

Ambient temperature	50 °C
Reduction factor	0.7
Mounting position	vertical
Power dissipation	5.9 W

### Power dissipation, single housing at 60 °C

Ambient temperature	60 °C
Reduction factor	0.57
Mounting position	vertical
Power dissipation	4.8 W

### Mechanical strength/tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Number of drop cycles	50

### Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 - 60.1 Hz)
Acceleration	5 g (60.1 - 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

### Shock

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

### Thermostability (Ball Thrust Test)

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20

### Test for assessing the risk of fire (glow wire)

# Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

## Technical data

### Test for assessing the risk of fire (glow wire)

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

### Test for substances that would hinder coating with paint or varnish

Specification	VW PV 3.10.7:2005-02
---------------	----------------------

### Degrees of protection provided by housings (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
Result, degree of protection, IP code	IP20

### General information

Type of note	Assembly instruction:
Note	Refer to the data sheet for the range in the download area.
Type of note	Recommendation
Note	Material of contact pads for bus connector, galvanic gold (hard gold)

### Packaging information

Type of packaging	packed in cardboard
Pieces per package	10
Denomination packing units	Pcs.
Outer packaging type	Carton

### Standards and regulations

Flammability rating according to UL 94	V0
--	----


### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

# Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 5.0	27371300
eCl@ss 5.1	27371300
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031

# Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

## Classifications

### ETIM

ETIM 7.0	EC001031
----------	----------

### UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Approvals

### Approvals

---

Approvals


UL Recognized

---

Ex Approvals

---

### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 240868
---------------	---	---	---------------

## Accessories

### Accessories

Component housing upper part

Housing cover - ME-IO 18,8 C 2U 7035 - 2201799



DIN rail housing, 2U, Housing cover, width: 18.9 mm, height: 21.8 mm, color: light gray (7035)

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Housing cover - ME-IO 18,8 C 3U 7035 - 2201800



DIN rail housing, 3U, Housing cover, width: 18.9 mm, height: 32.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 3U S1 7035 - 2201801



DIN rail housing, 3U, Housing cover, width: 18.9 mm, height: 32.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 4U 7035 - 2201802



DIN rail housing, 4U, Housing cover, width: 18.9 mm, height: 43.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 5U 7035 - 2201803



DIN rail housing, 5U, Housing cover, width: 18.9 mm, height: 54.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 6U 7035 - 2201804



DIN rail housing, 6U, Housing cover, width: 18.9 mm, height: 65.8 mm, color: light gray (7035)

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Housing cover - ME-IO 18,8 C 7U 7035 - 2201805



DIN rail housing, 7U, Housing cover, width: 18.9 mm, height: 76.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 8U 7035 - 2202634



DIN rail housing, 8U, Housing cover, width: 18.9 mm, height: 87.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 10U 7035 - 2202630



DIN rail housing, 10U, Housing cover, width: 18.9 mm, height: 109.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 2U MC10 7035 - 2202582



DIN rail housing, 2U for marking lid, Housing cover, width: 18.9 mm, height: 21.9 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 C 2U MC18 7035 - 2202581



DIN rail housing, 2U for marking lid, Housing cover, width: 18.9 mm, height: 21.9 mm, color: light gray (7035)

---



## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Housing cover - ME-IO 37,6 C 10U 7035 - 2202665



DIN rail housing, 10U, Housing cover, width: 37.89 mm, height: 109.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 56,4 C 10U 7035 - 2202662



DIN rail housing, 10U, Housing cover, width: 56.88 mm, height: 109.8 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 LC 8U 7035 - 2202622



DIN rail housing, L-type, Housing cover, width: 20.94 mm, height: 114.1 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 LC 10U 7035 - 2202626



DIN rail housing, L-type, Housing cover, width: 20.94 mm, height: 114.1 mm, color: light gray (7035)

---

Housing cover - ME-IO 18,8 F-LR 7035 - 2202635



DIN rail housing, Filler plugs, Housing cover, width: 11.7 mm, height: 16.1 mm, color: light gray (7035)

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Housing cover - ME-IO P 10U 7035 - 2202629



DIN rail housing, Partition plate, Housing cover, width: 2.69 mm, height: 112.2 mm, color: light gray (7035)

---

### DIN rail connector

DIN rail bus connectors - ME 18,8 TBUS 1,5/5-ST-3,81KMGY - 2201813



DIN rail connector, number of positions: 5, pitch: 3.81 mm, color: light gray, contact surface: Gold, Articles with gold-plated contacts, bus connectors for connecting with electronic housings

---

DIN rail bus connectors - TBUS8-18,8-PPPPPPPP-7035 - 2202396



DIN rail connector, number of positions: 8, pitch: 2.54 mm, color: light gray, 8 parallel contacts

---

DIN rail bus connectors - TBUS8-18,8-PPPPPPPS-7035 - 2202399



DIN rail connector, number of positions: 8, pitch: 2.54 mm, color: light gray, 7 parallel contacts/1 series contact

---

DIN rail bus connectors - TBUS8-18,8-PPPPPPSS-7035 - 2202403



DIN rail connector, number of positions: 8, pitch: 2.54 mm, color: light gray, 6 parallel contacts/2 series contacts

---

### Fiber optic

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Fiber optic - HS LC-H-D2/ R2XC1-2,54 - 2202316



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R2XC2-2,54 - 2202317



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R2XC5-2,54 - 2202318



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R2XC10-2,54 - 2202319



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R4XC2-2,54 - 2202320



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Fiber optic - HS LC-H-D2/ R4XC5-2,54 - 2202321



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R4XC9-2,54 - 2202322



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R4XC10-2,54 - 2202323



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R2XC4-2,54 - 2202531



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

Fiber optic - HS LC-H-D2/ R4XC4-2,54 - 2202532



Light guides, passive, rigid, can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed)

---

### Filler plug

Filler plugs - ME B-22,5 MSTBO BU 5010 - 2202235

DIN rail housing, Filler plug for unoccupied terminal points, color: blue (5010)

# Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

## Accessories

---

### Ground contact

Functional earth ground contact - ME BUS FE CONTACT - 2278076



DIN rail housing, FE contact

---

### Mounting material

Cover - ME-IO 18,8 MC 8U TRANS - 2202627



DIN rail housing, 8U, Marking lid, width: 18.8 mm, height: 110.95 mm

---

Locking - HSC-LR 9U KIT 2003 - 2201794



DIN rail housing, 9U, Lock and Release system, width: 16.1 mm, height: 111.8 mm, depth: 8.8 mm, color: orange (2003)

---

Locking - HSC-LR 7U KIT 2003 - 2201795



DIN rail housing, 7U, Lock and Release system, width: 16.1 mm, height: 89.95 mm, depth: 8.8 mm, color: orange (2003)

---

Locking - HSC-LR 5U KIT 2003 - 2201796



DIN rail housing, 5U, Lock and Release system, width: 16.1 mm, height: 67.95 mm, depth: 8.8 mm

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Locking - HSC-LR 3U KIT 2003 - 2201797



DIN rail housing, 3U, Lock and Release system, width: 16.1 mm, height: 45.95 mm, depth: 8.8 mm

---

Base latch - ME-IO 18,8 FOOT CATCH KIT - 2201812



Base latch, for DIN rail mounting, with spring included

---

Cover - ME-IO 18,8 MC 8U TRANS - 2202627



DIN rail housing, 8U, Marking lid, width: 18.8 mm, height: 110.95 mm

---

### PCB headers

Feed-through header - HSCH 2,5-3U/12 9005 - 2201788



PCB headers, number of positions: 12, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering

---

Feed-through header - HSCH 2,5-2U/ 8 9005 - 2201789



PCB headers, number of positions: 8, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering,  
Please observe the derating curve of the item

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Feed-through header - HSCH 2,5-2U-TTTT 9005 - 2201790



PCB headers, number of positions: 4, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering, Please observe the derating curve of the item

---

Feed-through header - HSCH 2,5-2U-2220 9005 - 2201792



PCB headers, number of positions: 6, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering, Please observe the derating curve of the item

---

Feed-through header - HSCH 1,5-3U/18 9005 - 2202232



HSC header, touch-proof, 3 units, 18 connections, please note the positioning, color: black

---

Feed-through header - HSCH 1,5-2U/12 9005 - 2202233



PCB headers, nominal current: 8 A, rated voltage (III/2): 30 V, nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 12, pitch: 3.45 mm, color: black, contact surface: Tin, Please observe the derating curve of the item

---

### PCB plug

Printed-circuit board connector - HSCP-SP 2,5-1U4-7035 - 2201780



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: orange

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

#### Printed-circuit board connector - HSCP-SP 2,5-1UTT-7035 - 2201781



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 2, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: orange

---

#### Printed-circuit board connector - HSCP-SP 2,5-1U20-7035 - 2201782



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 2, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Please observe the derating curve of the item

---

#### Printed-circuit board connector - HSCP-SP 2,5-1U-00 CPX - 2202585



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, connection method: Push-in spring connection

---

#### Printed-circuit board connector - HSCP-SP 2,5-1UTT-55/55-7035 - 2202607



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 2, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: green

---

#### Printed-circuit board connector - HSCP-SP 2,5-1U4-00/00-7035 - 2202569



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: black

---



## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Printed-circuit board connector - HSCP-SP 2,5-1U4-22/22-7035 - 2202572



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: red

Printed-circuit board connector - HSCP-SP 2,5-1U4-66/66-7035 - 2202570



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: blue

Printed-circuit board connector - HSCP-SP 2,5-1U4-55/55-7035 - 2202571



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: green

Printed-circuit board connector - HSCP-SP 2,5-1U4-99/99-7035 - 2202568



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring lever: white

Printed-circuit board connector - HSCP-SP 2,5-1UTT-62/62-7035 - 2202606



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 2, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring levers: blue / red

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Printed-circuit board connector - HSCP-SP 2,5-1U4-69/69-7035 - 2202605



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring levers: blue / white

---

Printed-circuit board connector - HSCP-SP 2,5-1U4-99/62-7035 - 2202608



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin, Color of the spring levers: white / blue / white / red

---

Printed-circuit board connector - HSCP-SP 2,5-1U4-29/29-7035 - 2203192



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin

---

Printed-circuit board connector - HSCP-SP 2,5-1U4-62/59-7035 - 2203194



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin

---

Printed-circuit board connector - HSCP-SP 2,5-1U4-65/65-7035 - 2203195



PCB connector, nominal current: 8 A, rated voltage (III/2): 300 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 4, pitch: 5 mm, connection method: Push-in spring connection, color: light gray, contact surface: Tin

---

## Mounting base housing - ME-IO 75,2 LB 10U TBUS 7035 - 2202620

### Accessories

Printed-circuit board connector - HSCP-SP 1,5-1U6-7035 - 2202234



PCB connector, nominal current: 8 A, rated voltage (III/2): 320 V, nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 6, pitch: 3.45 mm, connection method: Push-in spring connection, color: light gray, Color of the spring lever: orange

---

Printed-circuit board connector - HSCP-SP 1,5-1U6-629/629-7035 - 2202609



PCB connector, nominal current: 8 A, rated voltage (III/2): 320 V, nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 6, pitch: 3.45 mm, connection method: Push-in spring connection, color: light gray, Color of the spring levers: blue / red / white