

Button lens, flush, non-standard inscription

Part no. M22-XDL-*-*
Catalog No. 216446
Alternate Catalog No. -

Delivery program

Product range		Accessories
Basic function accessories		Button lenses
Description		≤ 5 characters: letter height 5 mm > 5 characters: letter height 3 mm
Design		Flush
Name		with customized inscription using the Label Editor → Data sheet, additional product information (links)
Selection to		Blank
For use with		M22(S)-DL-X M22(S)-DRL-X M22S-DGL-X M30C-FDL-X M30C-FDRL-X
Connection to SmartWire-DT		no


Notes

When ordering, the part no must include the following details:


1st wildcard * Δ color: -R, -G, -B, -W, -Y

2nd wildcard * Δ file name specified by Labeleditor

Text size 3 mm:
 max. 8 characters in 1st line, 10 characters in 2nd line, 8 characters in 3rd line



Text size 5 mm:
 Max. 5 characters per line



Technical data

General

Ambient temperature		
Open	°C	-25 - +70

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I _n	A	0
Heat dissipation per pole, current-dependent	P _{vid}	W	0
Equipment heat dissipation, current-dependent	P _{vid}	W	0
Static heat dissipation, non-current-dependent	P _{vs}	W	0
Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Please enquire
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9 Insulation properties		
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		Not applicable.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Hood/lens for circuit control devices (EC001072)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Dome, refractor (ec@ss10.0.1-27-37-12-31 [AKF049014])			
Colour lens			Other
Lens shape			Round
Construction type			Flat
Labelled			Yes
Built-in diameter		mm	22.5
Diameter		mm	22.2
Width		mm	0
Height		mm	2.5

Approvals

North America Certification		UL/CSA certification not required
-----------------------------	--	-----------------------------------

Additional product information (links)

IL04716002Z (AWA1160-1745) RMQ-Titan System	
IL04716002Z (AWA1160-1745) RMQ-Titan System	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2018_10.pdf
Notes on individual inscription using the Labeleditor software	http://de.ecat.moeller.net/flip-cat/?edition=HPLTEv1&startpage=2.53
RMQ-Titan symbol code	http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_1168307.pdf
f1=1454&f2=1179;Labeleditor	http://applications.eaton.eu/sdlc?LX=11&amp