



**Three-phase commoning link, Circuit-breaker: 5, 261 mm, For PKZM0-... or PKE12, PKE32 without side mounted auxiliary contacts or voltage releases**

**Part no.** B3.1/5-PKZ0  
**Catalog No.** 044948  
**Alternate Catalog No.** XTPAXCLKB5  
**EL-Nummer (Norway)** 4357232

### Delivery program

|   |  |        |  |
|---|--|--------|--|
| Product range   |  |        | Accessories  |
| Accessories   |  |        | Three-phase commoning link   |
|   |  |        | Protected against accidental contact, short-circuit proof, $U_e = 690\text{ V}$ , $I_u = 63\text{ A}$<br>Can be extended by rotating by installation<br>For PKZM0-... or PKE attached on the right with an auxiliary contact or trip indicating signal |
| For use with  |  |        | Three-phase commoning link PKZ0, PKE12, PKE32  |
| Circuit-breaker   |  | Number | 5  |
| Length  |  | mm     | 261  |
| Unit width  |  | mm     | 45 + 9   |
| <b>Notes</b>  |  |        |  |
| For parallel power feed to several motor-protective circuit-breakers on terminals 1, 3, 5 |  |        |  |

### Technical data

#### Main conducting paths

|                                       |           |      |       |
|---------------------------------------|-----------|------|-------|
| Rated impulse withstand voltage       | $U_{imp}$ | V AC | 6000  |
| Overtoltage category/pollution degree |           |      | III/3 |
| Rated operational voltage             | $U_e$     | V AC | 690   |
| Rated uninterrupted current           | $I_u$     | A    | 63    |

### Design verification as per IEC/EN 61439

|  |            |    |  |
|--|------------|----|--|
| Technical data for design verification   |            |    |  |
| Rated operational current for specified heat dissipation   | $I_n$      | A  | 63   |
| Heat dissipation per pole, current-dependent   | $P_{vid}$  | W  | 2.8  |
| Equipment heat dissipation, current-dependent  | $P_{vid}$  | W  | 8.4  |
| Static heat dissipation, non-current-dependent   | $P_{vs}$   | W  | 0  |
| Heat dissipation capacity  | $P_{diss}$ | W  | 0  |
| Operating ambient temperature min.   |            | °C | -25  |
| Operating ambient temperature max.   |            | °C | 55   |
| IEC/EN 61439 design verification   |            |    |  |
| 10.2 Strength of materials and parts   |            |    |  |
| 10.2.2 Corrosion resistance  |            |    | Meets the product standard's requirements.                         |
| 10.2.3.1 Verification of thermal stability of enclosures   |            |    | Meets the product standard's requirements.                         |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat   |            |    | Meets the product standard's requirements.                         |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |            |    | Meets the product standard's requirements.                         |
| 10.2.4 Resistance to ultra-violet (UV) radiation   |            |    | Meets the product standard's requirements.                         |
| 10.2.5 Lifting   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions  |            |    | Meets the product standard's requirements.                         |
| 10.3 Degree of protection of ASSEMBLIES  |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 Clearances and creepage distances   |            |    | Meets the product standard's requirements.                         |
| 10.5 Protection against electric shock   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components   |            |    | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections  |            |    | Is the panel builder's responsibility.                             |

|  |  |  |  |
|--|--|--|--|
| 10.8 Connections for external conductors                 |  |  | Is the panel builder's responsibility.   |
| 10.9 Insulation properties                               |  |  |  |
| 10.9.2 Power-frequency electric strength                 |  |  | Is the panel builder's responsibility.   |
| 10.9.3 Impulse withstand voltage                         |  |  | Is the panel builder's responsibility.   |
| 10.9.4 Testing of enclosures made of insulating material |  |  | Is the panel builder's responsibility.   |
| 10.10 Temperature rise                                   |  |  | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating                               |  |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility                      |  |  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function                                |  |  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |



## Technical data ETIM 7.0

|  |  |                 |      |
|--|--|-----------------|------|
| Low-voltage industrial components (EG000017) / Phase busbar (EC000215)   |  |                 |      |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ecl@ss10.0.1-27-37-13-06 [ACN992011]) |  |                 |      |
| Number of phases   |  |                 | 3    |
| Number of poles  |  |                 | 3    |
| Suitable for number of devices   |  |                 | 5    |
| Pitch dimensions   |  | mm              | 54   |
| Cross section  |  | mm <sup>2</sup> | 0    |
| Length   |  | mm              | 261  |
| Number of modular spacings   |  |                 | 0    |
| Rated permanent current I <sub>u</sub>   |  | A               | 63   |
| Type of electric connection  |  |                 | Fork |
| Insulated  |  |                 | Yes  |
| Rated surge voltage  |  | kV              | 6    |
| Conditioned rated short-circuit current I <sub>q</sub>   |  | kA              | 0    |
| Max. rated operation voltage U <sub>e</sub>  |  | V               | 690  |
| Rated short-time withstand current I <sub>cw</sub>   |  | kA              | 0    |
| Suitable for devices with N-busbar   |  |                 | No   |
| Suitable for devices with auxiliary switch   |  |                 | No   |

## Approvals

|                                      |  |  |  |
|--------------------------------------|--|--|--|
| Product Standards                    |  |  | UL 508; CSA-C22.2 No. 14; IEC60947-4-1; CE marking |
| UL File No.                          |  |  | E36332   |
| UL Category Control No.              |  |  | NLRV   |
| CSA File No.                         |  |  | 98494  |
| CSA Class No.                        |  |  | 3211-06  |
| North America Certification          |  |  | UL listed, CSA certified                           |
| Specially designed for North America |  |  | No   |

## Dimensions



Three-phase commoning link

## Additional product information (links)

Motor starters and "Special Purpose Ratings" for the North American market

[http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct\\_3258146.pdf](http://www.eaton.eu/ecm/groups/public/@pub/@europe/@electrical/documents/content/pct_3258146.pdf)

Busbar Component Adapters for modern Industrial control panels

[http://www.moeller.net/binary/ver\\_techpapers/ver960en.pdf](http://www.moeller.net/binary/ver_techpapers/ver960en.pdf)