


Measuring instrument - EEM-350-D-MCB - 2905849

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Three-phase energy meter for real power measurement in networks up to 460 V / 65 A, with 3 digital inputs and RS-485 interface, certified according to the MID directive

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 000855
GTIN	4055626000855
Weight per Piece (excluding packing)	398.400 g
Custom tariff number	90303370
Country of origin	Italy

Technical data

Dimensions

Width	72 mm
Height	90 mm
Depth	67 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-30 °C ... 70 °C
Permissible humidity (storage/transport)	0 % ... 90 %
Max. permissible relative humidity (operation)	< 90 %
Degree of protection	IP50 (Front)
	IP20 (Back side)

Input data

Measuring principle	True r.m.s. value measurement
Measured value	AC sine (50/60 Hz)
Input name	Voltage measuring input V1, V2, V3

Measuring instrument - EEM-350-D-MCB - 2905849

Technical data

Input data

Input voltage range	196 V AC ... 460 V AC (Phase/Phase)
	113 V AC ... 265 V AC (Phase/neutral conductor)
Surge voltage capacity	460 V AC (Permanent)
Precision	0.5 % (Phase/neutral conductor)
Input name	Current measuring input I1, I2, I3
Input current	10 A (scaled nominal current)
	65 A (I_{max})
Overload capacity	1920 A (10 ms)
Precision	0.5 %
	1 % (Effective and apparent power)
Reactive power (IEC 62053-23)	Class 2
Description of the input	Digital input
Number	3
Voltage input signal	5 V DC \pm 5 %

Interfaces

Designation	Modbus RTU/JBUS
Interface	RS-485
Connection method	Screw terminal blocks

General

Display	LCD display
Measuring rate	750 ms
Supply voltage range	Measurement voltage supply
Power consumption	\leq 12 VA (2 W)
Mains type	3-phase (4-conductor)
Color	black
Conformance	CE-compliant
Rated insulation voltage	300 V AC (EN 61010-1)
Test voltage	4 kV AC (50 Hz, 1 min.)

Standards and Regulations

Conformance	CE-compliant
MID	Attachment V

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27271100
------------	----------

Measuring instrument - EEM-350-D-MCB - 2905849

Classifications

eCl@ss

eCl@ss 5.0	27200300
eCl@ss 5.1	27200300
eCl@ss 6.0	27142300
eCl@ss 7.0	27142330
eCl@ss 8.0	27142330
eCl@ss 9.0	27142330

ETIM

ETIM 4.0	EC002301
ETIM 5.0	EC002301
ETIM 6.0	EC002301
ETIM 7.0	EC002301

Approvals

Approvals

Approvals

PTB-BG / EAC

Ex Approvals

Approval details

PTB-BG	DE-14- MI003-PTB002
--------	------------------------

EAC		RU *- DE.A*30.B.01628
-----	--	--------------------------