

DIN rail perforated - NS 15 BLK PERF 2000MM - 1401608


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, Standard profile, width: 15 mm, height: 5.5 mm, acc. to EN 60715, material: Steel, uncoated, length: 2000 mm, color: white aluminum



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| GTIN |  4 017918 167356 |
| GTIN | 4017918167356 |
| Weight per Piece (excluding packing) | 284.000 g |
| Custom tariff number | 72166190 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------------------|----------|
| Height | 5.5 mm |
| Length | 2000 mm |
| Width | 15 mm |
| Hole width | 12.20 mm |
| Hole height | 4.20 mm |
| Drill hole spacing | 20.00 mm |

General

| | |
|----------|----------------|
| Material | Steel |
| Coating | uncoated |
| Color | white aluminum |

Standards and Regulations

| | |
|---------------|------------------|
| Test standard | acc. to EN 60715 |
|---------------|------------------|

DIN rail perforated - NS 15 BLK PERF 2000MM - 1401608


Technical data

Standards and Regulations

| | |
|----------------------------------|----------|
| Connection in acc. with standard | IEC / EN |
|----------------------------------|----------|

Drawings

Dimensional drawing



Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27110800 |
| eCl@ss 4.1 | 27110800 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |

DIN rail perforated - NS 15 BLK PERF 2000MM - 1401608

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 6.0 | 27400600 |
| eCl@ss 7.0 | 27400602 |
| eCl@ss 8.0 | 27400602 |
| eCl@ss 9.0 | 27400602 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001285 |
| ETIM 3.0 | EC001285 |
| ETIM 4.0 | EC000212 |
| ETIM 5.0 | EC000212 |
| ETIM 6.0 | EC001285 |
| ETIM 7.0 | EC001285 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 39121708 |
| UNSPSC 11 | 39121708 |
| UNSPSC 12.01 | 39121708 |
| UNSPSC 13.2 | 39121708 |
| UNSPSC 18.0 | 39121708 |
| UNSPSC 19.0 | 39121708 |
| UNSPSC 20.0 | 39121708 |
| UNSPSC 21.0 | 39121708 |