

DIN rail perforated - NS 35/15 WH PERF(5,2X25)2000MM - 1206476


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, Galvanized, white passivated, length: 2000 mm, Hole size: 5.2 x 25 mm, color: silver

RoHS

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| GTIN |  4 017918 170899 |
| GTIN | 4017918170899 |
| Weight per Piece (excluding packing) | 1,200.000 g |
| Custom tariff number | 72166190 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------------------|----------|
| Height | 15 mm |
| Length | 2000 mm |
| Width | 35 mm |
| Hole width | 25.00 mm |
| Hole height | 5.20 mm |
| Drill hole spacing | 36.00 mm |

General

| | |
|----------|------------------------------|
| Material | Steel |
| Coating | Galvanized, white passivated |
| Color | silver |

Standards and Regulations

| | |
|---------------|---------------------|
| Test standard | similar to EN 60715 |
|---------------|---------------------|

DIN rail perforated - NS 35/15 WH PERF(5,2X25)2000MM - 1206476

Technical data

Standards and Regulations

| | |
|----------------------------------|----------|
| Connection in acc. with standard | IEC / EN |
|----------------------------------|----------|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27110800 |
| eCl@ss 4.1 | 27110800 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27400600 |
| eCl@ss 7.0 | 27400602 |
| eCl@ss 8.0 | 27400602 |
| eCl@ss 9.0 | 27400602 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001285 |
| ETIM 3.0 | EC001285 |
| ETIM 4.0 | EC000212 |
| ETIM 5.0 | EC000212 |
| ETIM 6.0 | EC001285 |
| ETIM 7.0 | EC001285 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 39121708 |
| UNSPSC 11 | 39121708 |
| UNSPSC 12.01 | 39121708 |
| UNSPSC 13.2 | 39121708 |
| UNSPSC 18.0 | 39121708 |
| UNSPSC 19.0 | 39121708 |
| UNSPSC 20.0 | 39121708 |
| UNSPSC 21.0 | 39121708 |