

Shrink sleeve - WMS 2,4 (EX4)R CUS - 0800701

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white: user-defined, perforated, mounting type: slide-on, cable diameter range: 0.8 ... 2.4 mm, lettering field size: max. 30 mm

Your advantages

- ✓ Individual labels can be ordered with a maximum length of 30 mm
- ✓ MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- ✓ UL 224 (125°C, 600 V, all tubing)



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 628341
GTIN	4046356628341
Weight per Piece (excluding packing)	0.300 g
Custom tariff number	49119900
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	30 m
Width (a)	4 mm
Cable diameter	0.8 mm ... 2.4 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Shrink sleeve - WMS 2,4 (EX4)R CUS - 0800701

Technical data

General

Color	white
Base element material	polyolefine
Type	Shrink sleeve
Components	halogen-free
Material	Polyolefine
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	user-defined
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	slide-on

Standards and Regulations

Connection in acc. with standard	CSA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Classifications

eCl@ss

eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27400100
eCl@ss 5.1	27400100
eCl@ss 6.0	27400100
eCl@ss 7.0	27400105
eCl@ss 8.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC001530
ETIM 5.0	EC000217

Shrink sleeve - WMS 2,4 (EX4)R CUS - 0800701

Classifications

ETIM

ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

CSA / UL Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	252259
-----	--	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	--	---	---------------