

## **TECHNICAL DATA SHEET**

Part#: 7375E

Cutters - Angulated Head -★★★★- Carbon Steel - Blade Length .125"

The 7375E five star Lazer Line® sub-miniature angulated/tapered maximum flush cutter with a cutting capacity of .001" - .010" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. This 4.25" tool has a 40 angled/tapered head. The set-screw prevents over-travel while prolonging the life of the tool.

Precision Level

Material

Surface Resistivity

Shape

Type of Cut

• Group

Cutting Capacity

• Blade Angle

• Blade Length

• Body Width

Body Height

OAL

• Weight (OZ)

UPC

Schedule B

• ECCN • UNSPSC Code

Country of Origin

\*\*\*\*

Carbon

10<sup>8</sup> ohms/sq

Angulated Head

Lazer Flush

**Cutting Tools** 

50 - 30 AWG / .001 - .010" / .03 - .25 mm

50°

.08" (2mm)

0.32" (8mm)

0.20" (5mm)

4.25" (106.25mm)

3

662847013393

8203.20.60.60

EAR99

27111511

**USA** 











