

## Product information


# 76 81 125

## Diagonal Cutter

For electromechanics

DIN ISO 5749

- With sharp, precisely aligned cutting edges for soft, hard wire and piano wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- Lap joint
- Particularly tapered head with small bevel for work in confined areas (cable harnesses, multiple stranded wires)
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	76 81 125
EAN	4003773040644
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	88 g
Dimensions	125 x 78 x 33 mm
Standard	DIN ISO 5749
Technische Attribute	
Style	8
Cutting capacities medium hard wire (diameter)	Ø 1.3 mm
Cutting capacities hard wire (diameter)	Ø 0.8 mm
Cutting capacities soft wire (diameter)	Ø 0.4 – 1.7 mm
	16 mm
	9 mm
Head width	14.5 mm
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted