

Cisco Industrial Ethernet 2000 Series Switches

Product Overview

The Cisco® Industrial Ethernet 2000 (IE 2000) Series is a range of compact, ruggedized access switches that handle security, voice, and video traffic across industrial networks. They provide customers in industries such as automotive, oil and gas, mining, transportation, and energy with highly secure access and industry-leading convergence using Cisco Resilient Ethernet Protocol (REP).

Product Details

The Cisco IE 2000 Series are designed for low cost, low ports, and small sizes. They offer:

- Four, eight, or 16 10/100Base-T Ethernet ports (Small Form-Factor Pluggable [SFP] downlinks on selected models); fixed configurations with a compact form factor
- Two gigabit combo ports: SFP (100 Mbps and 1 Gbps) or RJ45 uplink
- Dual-input DC power supply, alarm relays, DIN rail mount
- Industrial Power over Ethernet (PoE) solution
- · Conformal coating available
- Swappable SD flash card and mini-USB connector
- Industrial environmental compliance and certifications
- Industrial partner applications: Ethernet/IP and PROFINET

Primary Benefits and Features

- Easy deployment: Zero-touch discovery using Dynamic Host Control Protocol (DHCP), express setup, and fast bootup time (60 seconds) to help in migrating to an Ethernet environment without resistance.
- Security: 802.1x, port security, and DHCP allow dynamic port-based authentication; Secure Shell (SSHv2); SNMPv3 provides encrypted administrator traffic during Telnet and SNMP sessions; TACACS+ and RADIUS authentication facilitate centralized control and restrict unauthorized users.
- Resiliency: Cisco REP ring protocol and PROFINET Media Redundancy Protocol (MRP)
- Manageability: Auto SmartPort, Web Device Manager, Telnet, HTTPS access, SNMP, CNA, and Cisco Prime Infrastructure.
- **Network Address Translation (NAT):** Line-rate, hardware-enabled 1:1 static address translation designed to enable duplicate IP address usage in the Layer 2 machine node networks.
- Layer 3 routing: IPv4 and IPv6.
- Industrial PoE: PoE (IEEE 802.af) and PoE+ (802.3at) supported on selected models.
- Industrial automation protocols: EtherNet/IP (CIP) and PROFINET MRP (IEC 62439-2) allow integration with existing management platforms from Rockwell, Siemens, and others.

Product Specifications

Switch Performance and Scalability

- Maximum Forwarding Bandwidth 3.8Gbps
- Maximum Switching Bandwidth 7.6Gbps
- Maximum Forwarding rate: 5.66Mpps with 64-byte packets (Line-rate at all packet sizes)
- Egress buffer: 2 MB
- Unicast MAC addresses: 8000
- Internet Group Management Protocol (IGMP) multicast groups: 255
- Maximum virtual LANs (VLANs): 1005
- IPv4 MAC security ACEs: 384 (default ternary content-addressable memory [TCAM] template)
- Bidirectional, 128 NAT translation entries
- IPv4 routing: 3500 routes, IPv6 routing: 1750 routes

Detailed Product Information

Figure 1 shows switch models, and Table 1 shows the Cisco IE 2000 Series configuration information. Table 2 lists the SKUs for power supplies and license upgrades. Table 3 includes IE 2000 Series product specifications. Table 4 lists software features. Table 5 includes compliance specifications. Table 6 outlines management and relevant industry standards.

Figure 1. Industrial Ethernet 2000 Series



6 copper ports or 4 copper ports, plus 2 SFP



6 fiber ports



8 copper ports plus 2 combo ports (copper or SFP)



16 copper plus 2 combo ports



16 copper ports (including 4 PoE/PoE+ ports), plus 2 combo ports

 Table 1.
 Industrial Ethernet 2000 Series Configurations

Product Number	Total Ports	RJ45 Ports	Combo Ports	SFP Ports	Manufacturing License	Type of possible Upgrade	IEEE 1588	L2NAT	PoE/ PoE(+)	Conformal Coating
IE-2000-4TS-L	6	4 FE		2 FE	LAN Lite	3				
IE-2000-4TS-B	6	4 FE		2 FE	LAN Base	1				
IE-2000-4T-L	6	6 FE			LAN Lite	3				
IE-2000-4T-B	6	6 FE			LAN Base	1				
IE-2000-4TS-G-L	6	4 FE		2 GE	LAN Lite	3				
IE-2000-4TS-G-B	6	4 FE		2 GE	LAN Base	1				
IE-2000-4T-G-L	6	4 FE, 2 GE			LAN Lite	3				
IE-2000-4T-G-B	6	4 FE, 2 GE			LAN Base	1				

Product Number	Total Ports	RJ45 Ports	Combo Ports	SFP Ports	Manufacturing License	Type of possible Upgrade	IEEE 1588	L2NAT	PoE/ PoE(+)	Conformal Coating
IE-2000-4S-TS-G-L	6			4 FE, 2 GE	LAN Lite	3				
IE-2000-4S-TS-G-B	6			4 FE, 2 GE	LAN Base	1, 3				
IE-2000-8TC-L	10	8 FE	2 FE		LAN Lite	3				
IE-2000-8TC-B	10	8 FE	2 FE		LAN Base	1				
IE-2000-8TC-G-L	10	8 FE	2 GE		LAN Lite	3				
IE-2000-8TC-G-B	10	8 FE	2 GE		LAN Base	1				
IE-2000-8TC-G-E	10	8 FE	2 GE		LAN Base	1, 2, 4	Yes	U [*]		
IE-2000-16TC-L	20	16 FE	2 FE	2 FE	LAN Lite	3				
IE-2000-16TC-B	20	16 FE	2 FE	2 FE	LAN Base	1				
IE-2000-16TC-G-L	20	16 FE	2 GE	2 FE	LAN Lite	3				
IE-2000-16TC-G-E	20	16 FE	2 GE	2 FE	LAN Base	1, 2, 4	Yes	U [*]		
IE-2000-16TC-G-X	20	16 FE	2 GE	2 FE	LAN Base	1, 2, 4	Yes	U [*]		Yes
IE-2000-8TC-G-N	10	8 FE	2 GE		Enhanced LAN Base	1, 2	Yes	Yes		
IE-2000-16TC-G-N	20	16 FE	2 GE	2FE	Enhanced LAN Base	1, 2	Yes	Yes		
IE-2000-16PTC-G-L	18	16 FE	2 GE		LAN Lite	3			Yes	
IE-2000-16PTC-G-E	18	16 FE	2 GE		LAN Base	1, 2	Yes	U	Yes	
IE-2000-16PTC-G- NX	18	16 FE	2 GE		Enhanced LAN Base	1, 2	Yes	Yes	Yes	Yes

[&]quot;Type of possible Upgrade" Legend:

- 1: LAN Base to IP Lite Cisco IOS Software Upgrade
- 2: Enhanced LAN Base to IP Lite Cisco IOS Softw are Upgrade
- 3: LAN Lite to LAN Base Cisco IOS Software Upgrade
- 4: LAN Base to Enhanced LAN Base Cisco IOS Software Upgrade and License Upgrade
- U: Upgradable to L2NAT via Enhanced Lan Base or IP Lite license

 Table 2.
 Accessories and License Upgrade PIDs

Product Number	Description
SD-IE-1GB=	1 GB Ruggedized SD memory card (must be ordered, not included by default)
STK-RACK-DINRAIL=	19 in. DIN Rail mount kit
L-IE2000-L-B=	IE2000 LAN Lite to LAN Base e-license
L-IE2000-B-E=	IE2000 LAN Base to Enhanced LAN Base e-license
LIC-IE2000-IP-L=	IE2000 LAN Base or Enhanced LAN Base to IPLite e-license
LIC-IE2000-L-IP=	IE2000 LAN Lite to IPLite e-license
LIC-MRP-MANAGER=	MRP Ring Manager license
LIC-MRP-Client=	MRP Ring Client license
Wallmount-IE2k-04=	Wall mount kit accessory for IE2000 4-ports downlink PID
Wallmount-IE2k-08=	Wall mount kit accessory for IE2000 8-ports downlink PID
Wallmount-IE2k-16=	Wall mount kit accessory for IE2000 16-ports downlink PID

 Table 3.
 Product Specifications

Description	Specification
Hardware	256 MB DRAM with ECC memory IEEE 1588v2FPGA 64 MB on-board flash memory 1GB remov able SD flash memory card (optional) Mini-USB connector
Alarm	Alarm I/O: Two alarm inputs to detect dry contact open or close; one alarm output relay
Power Consumption	 4-port downlink models: 9.5-15 W 8-port downlink models: 12.5-20 W 16-port downlink models: 21-30 W 4-port PoE/PoE+ models: 21-30 W (16-port base switch) and 4 PoE/PoE+ power requirement
Connectors and Cabling	 100BASE-FX MMF (2 km), -LX SMF (10 km) -ZX SMF (100 km), BX10 SMF (10 km) SFP and CWDM SFP- based ports: LC fiber connectors 10/100/1000BASE-T ports: RJ-45 connectors, 4-pair Category 5 UTP cabling
Dimensions (H x W x D) Including DIN Rail	 IE-2000 6 ports (copper downlinks) chassis: 5.1"H x 2.95"W x 4.51"D in (130mm H x 74.9mm W x 115mm D) IE-2000 6 ports (SFP downlinks) chassis: 5.1"H x 3.15"W x 4.51"D in (130mm H x 80mm W x 115mm D) IE-2000 10 ports short chassis: 5.1"H x 3.6"W x 4.51"D (130mm H x 91.4mm W x 115mm D) IE-2000 10 ports long chassis: 5.1"H x 3.6"W x 5.26"D (130mm H x 91.4mm W x 134mm D) IE-2000 18-20 ports chassis: 5.1"H x 5.0"W x 5.26"D (130mm H x 127mm W x 134mm D) PWR-IE50W-AC=: 5.8"H x 2.0"W x 4.4"D (147mm H x 51 mm W x 112mm D) PWR-65W-PC-AC=: 5.9 "H x 2.6"W x 4.6"D (150mm H x 66mm W x 117mm D) PWR-65W-PC-DC=: 5.9 "H x 2.6"W x 4.6"D (150mm H x 66mm W x 117mm D) PWR-IE170W-PC-AC=: 5.93 x 3.72 x 5.60 in. (150.6 x 94.5 x 142.2mm) PWR-IE170W-PC-DC=: 5.93 x 4.47 x 5.75 in. (150.6 x 113.5 x 145.8mm)
Weight	 IE-2000 6 ports chassis: 2.45 lbs (1.11 kg) IE-2000 6 ports (SFP): 2.69 lbs (1.22 kg) IE-2000 10 ports short chassis: 2.75 lbs (1.25 kg) IE-2000 10 ports long chassis: 3.45 lbs (1.56 kg) IE-2000 18-20 ports chassis: 4.35 lbs (1.97 kg) PWR-IE50W-AC=: 1.4 lb (0.65 kg) PWR-IE50W-AC-IEC=: 1.4 lb (0.65 kg) PWR-IE65W-PC-DC=: 2.6 (1.18 Kg) PWR-IE65W-PC-AC=: 2.7 (1.24 Kg) PWR-IE170W-PC-AC=: 3.88 pounds (1.76 kg) PWR-IE170W-PC-DC=: 3.7 pounds (1.67 kg)

Table 4.IE 2000 Series Pow er Supplies

Product Number	Wattage	Rated Nominal Input Operating Range	Supported Input Voltage Operating Range	Power Output	PoE/PoE+ Support	Use Case Scenario
PWR-IE170W- PC-AC=	170W	AC 100-240V/2.3A 50-60Hz or DC 125-250V/2.1A	AC 90-264V or DC 106-300V	54VDC/3.15A	Yes	Maximum PoE/PoE+ port support in a AC or high DC env ironment ¹
PWR-IE170W- PC-DC=	170W	DC 12-54V/23A	DC 10.8-60V	54VDC/3.15A	Yes	Maximum PoE/PoE+ port support in a DC environment ¹
PWR-IE50W- AC=	50W	AC 100-240V/1.25A 50-60Hz or DC 125-250V/1.25A	AC 90-264V or DC 106-300V	24VDC/2.1A	No	Provides power to main system, not used for PoE in an AC or high DC environment
PWR-IE50W- AC-IEC=	50W	AC 100-240V/1.25A 50-60Hz	AC 90-264V	24VDC/2.1A	No	Provides power to main system, not used for PoE in DC environment

Product Number	Wattage	Rated Nominal Input Operating Range	Supported Input Voltage Operating Range	Power Output	PoE/PoE+ Support	Use Case Scenario
PWR-IE65W-PC-AC=	65W	AC 100-240V/1.4A 50-60Hz or DC 125-250V/1.0A	AC 90-264V or DC 106-300V	54VDC/1.2 A	Yes	Supports up to 4 ports PoE or 2 ports PoE+ when used in PoE power input in an AC or high DC environment
PWR-IE65W-PC-DC=	65W	DC 24-48VDC/4.5A	DC 18-60V	54VDC/1.2 A	Yes	Supports up to 4 ports PoE or 2 ports PoE+ when used in PoE power input in a DC environment

¹ The 170W (both AC and DC) power supplies have enough power for the base unit and the PoE. Connect one power output from the 170W PSU to the main power input of the IE2000, and the other power output of the 170W PSU to the PoE power input of the IE2000.

Table 5. Cisco IE 2000 Softw are Features

LAN Lite License	Baseline Features
Layer 2 Switching	IEEE 802.1, 802.3, 802.3at, 802.3af standard (see Table 6), VTPv2, NTP, UDLD, CDP, LLDP, Unicast MAC filter, Resilient Ethernet Protocol (REP), Media Redundancy Protocol (MRP) Ring (IEC 62439-2)
Security	SCP, SSH, SNMPv3, TACACS+, RADIUS Server/Client, MAC Address Notification, BPDU Guard, SPAN session
Multicast	IGMPv1, v2, v3 Snooping, IGMP filtering, IGMP Querier
Management	Fast Boot, Express Setup, Web Device Manager, CNA, Cisco Prime, LMS, MIB, SmartPort, SNMP, syslog
Industrial Ethernet	EtherNet/IP, Profinet v2
LAN Base License	Additional Features
Layer 2 Switching	VTPv3, EtherChannel, Voice VLAN, Flexlink
Security	IPv4 Port-Security, DHCP Snooping, Dynamic ARP Inspection, IP Source Guard, 802.1x, Guest VLAN. MAC Authentication By pass, 802.1x Multi-Domain Authentication, Storm Control, Trust Boundary, Access-List (ACL), IPv6 MLD snooping
Quality of Service	IPv 4 Ingress Policing, Rate-Limit, Egress Queuing/Shaping, AutoQoS
Management	Port-Based DHCP, Storm Control - Unicast, Multicast, Broadcast, SPAN Sessions, RSPAN, DHCP Server, Customized TCAM/SDM Size Configuration, Embedded Event Manager (EEM)
Industrial Ethernet	IEEE 1588 PTPv 2
IPv4 Routing	IPv 4 static routing
IPv6 Routing	IPv 6 host support, HTTP over IPv 6, SNMP over IPv 6
Enhanced LAN Base	Additional Features
Industrial Management	Layer 2 switching with 1:1 static Network Address Translation (NAT)
IP Lite License	Additional Features
IPv4 Routing	RIP, OSPF, EIGRP, VRF Lite, PIM for L3 multicast routing including sparse (SM) and dense (DM) mode.
IPv6 Routing	IPv 6 Static routing, OSPFv 3
Security	FIPS 140-2
Embedded Event Manager	EEM feature enabled with IP Lite License

 Table 6.
 Compliance Specifications

Description	Specification
Safety Certifications	 UL/CSA 60950-1 EN 60950-1 CB to IEC 60950-1 (with country deviations) NOM to NOM-019-SCF1 (through partners and distributors) CE Marking
Hazard Location	 ANSI/ISA 12.12.01 (Class1, Div 2 A-D) EN 60079-0, -15 ATEX Certificate (Class 1, Zone2 A-D)

Description	Specification
	Cabinet enclosure required
EMC Emissions and Immunity Compliance	Cabinet enclosure required FCC 47 CFR Part 15 Class A EN 55022A Class A VCCI Class A RoHS compliance AS/NZS CISPR 22 Class A, AS/NZS CISPR 24 CISPR11 Class A, CISPR22 Class A KCC -Korea CE Marking C-Tick (Australia) Russia certification Brazil certification Brazil certification IEC/EN/EN61000-4-2 (Electro Static Discharge), 15kV air/8kV contact IEC/EN 61000-4-3 (Radiated Immunity, 10 and 20 V/m) IEC/EN 61000-4-4 (Fast Transients - 4kV power line, 4kV data line) IEC/EN 61000-4-5 (Surge 2 kV/1 kV) IEC/EN 61000-4-6 (Conducted Immunity, 10 V/emf) IEC/EN 61000-4-9 (Pulse Magnetic Field Immunity) IEC/EN 61000-4-10 (Oscillatory Magnetic Field Immunity) IEC/EN 61000-4-10 (AC power Voltage Immunity) IEC/EN 61000-6-20 (Voltage Dips Immunity) IEC/EN 61000-6-21 (Immunity for Industrial Environments) IEC/EN 61000-6-2 (Immunity for Industrial Environments)
Shock and Vibration	 EN 61326 IEC 60068-2-27 (Operational Shock: 30G 11ms, half sine) IEC 60068-2-27 (Non-Operational Shock 55-70G, trapezoidal) IEC 60068-2-6, IEC 60068-2-64, EN 61373 (Operational Vibration) IEC 60068-2-6, IEC 60068-2-64, EN 61373 (Non-operational Vibration)
Industry Standards	 UL508 CSA C22.2 No. 142 EN 61131-2 (EMC/EMI, environmental, mechanical) Protective coating (specific models only) Marine DnV Substation KEMA (IEEE 1613, IEC 61850-3) Railway EN 50155 (EMI/EMC, environmental, mechanical) EN50121-3-2 EN50121-4 NEMA TS-2 (EMC, environmental, mechanical) ABB Industrial IT certification IP30 ODVA Industrial Ethernet/IP support PROFINETV2.3 support
Corrosive Testing	• ISO-12944-6 • IEC-60068-2-60
Humidity	 IEC 60068-2-52 (salt fog mist, test Kb) marine environments IEC 60068 -2-3 IEC 60068-2-30 Relative humidity: 5% to 95% non-condensing
Operating Temperature	 -40C to +70C (vented enclosure - 40 LFM Air Flow) -40C to +60C (sealed enclosure - 0 LFM Air Flow) -34C to +75C (fan or blower-equipped enclosure - 200 LFM Air Flow) -40C to +85C (IEC 60068-2-2 Environmental Type Testing - 16 hours)

Description	Specification
	Operational altitude: Up to 15,000 ft
Storage Temperature	 -40 C to +85 C (storage temperature) IEC 60068-2-14 Storage altitude: Up to 15,000 ft
Mean Time Between Failure (MTBF)	Mean time between failure: 374,052 hours (42.7 years)
Warranty	• Five-year limited warranty on all IE-2000 HW PIDs and all IE Power Supplies defined in table 4 above. See link below for details on warranty

 Table 7.
 Management and Standards

Description	Specification	Specification
IEEE Standards	IEEE 802.1D MAC bridges, STP IEEE 802.1p Lay er 2 COS prioritization IEEE 802.1q VLAN IEEE 802.1s Multiple Spanning-Trees IEEE 802.1w Rapid Spanning-Tree IEEE 802.1x Port Access Authentication IEEE 802.1AB LLDP IEEE 802.3ad Link Aggregation (LACP) IEEE 802.3af Power ov er Ethernet provides up to 15.4W DC power to each end device IEEE 802.3at Power ov er Ethernet provides up to 25.5W DC power to each end device	IEEE 802.3af Power over Ethernet IEEE 802.3at Power over Ethernet Plus IEEE 802.3ah 100BASE-X SMF/MMF only IEEE 802.3a full duplex on 10Base-T IEEE 802.3 10BASE-T specification IEEE 802.3u 100BASE-TX specification IEEE 802.3ab 1000BASE-T specification IEEE 802.3ab 1000BASE-X specification IEEE 802.3z 1000BASE-X specification IEEE 1588v 2 PTP Precision Time Protocol
RFC Compliance	 RFC 768: UDP RFC 783: TFTP RFC 791: IPv 4 protocol RFC 792: ICMP RFC 793: TCP RFC 826: ARP RFC 854: Telnet RFC 951: BootP RFC 959: FTP RFC 1157: SNMPv 1 RFC 1901,1902-1907 SNMPv 2 RFC 2273-2275: SNMPv 3 RFC 2571: SNMP Management RFC 1166: IP Addresses RFC 1256: ICMP Router Discovery 	 RFC 1305: NTP RFC 1492: TACACS+ RFC 1493: Bridge MIB Objects RFC 1534 DHCP and BootP interoperation RFC 1542: Bootstrap Protocol RFC 1643: Ethernet Interface MIB RFC 1757: RMON RFC 2068: HTTP RFC 2131, 2132: DHCP RFC 2236: IGMP v2 RFC 3376: IGMP v3 RFC 2474: Diff Serv Precedence RFC 3580: 802.1x RADIUS RFC 4250-4252 SSH Protocol
Simple Network Management Protocol (SNMP) MIB Objects	BRIDGE-MIB CALISTA-DPA-MIB CISCO-ACCESS-ENVMON-MIB CISCO-ADMISSION-POLICY-MIB CISCO-BRIDGE-EXT-MIB CISCO-BRIDGE-EXT-MIB CISCO-CABLE-DIAG-MIB CISCO-CABLE-DIAG-MIB CISCO-CAR-MIB CISCO-CAR-MIB CISCO-CDP-MIB CISCO-CIRCUIT-INTERFACE-MIB CISCO-CUSTER-MIB CISCO-CONFIG-COPY-MIB CISCO-CONFIG-MAN-MIB CISCO-CONFIG-MAN-MIB CISCO-DATA-COLLECTION-MIB	CISCO-SNMP-TARGET-EXT-MIB CISCO-STACK-MIB CISCO-STACKMAKER-MIB CISCO-STP-EXTENSIONS-MIB CISCO-SYSLOG-MIB CISCO-TCP-MIB CISCO-UDLDP-MIB CISCO-VLAN-IFTABLE-RELATIONSHIP-MIB CISCO-VLAN-MEMBERSHIP-MIB CISCO-VTP-MIB ENTITY-MIB ETHERLIKE-MIB HC-RMON-MIB IEEE8021-PAE-MIB IEEE8023-LAG-MIB IF-MIB

Description	Specification	Specification
	CISCO-ENTITY-ALARM-MIB	• IP-MIB
	CISCO-ENTITY-VENDORTYPE-OID-MIB	LLDP-EXT-MED-MIB
	CISCO-ENVMON-MIB	• LLDP-MIB
	CISCO-ERR-DISABLE-MIB	NETRANGER
	CISCO-FLASH-MIB	NOTIFICATION-LOG-MIB
	CISCO-FTP-CLIENT-MIB	OLD-CISCO-CHASSIS-MIB
	CISCO-IF-EXTENSION-MIB	OLD-CISCO-CPU-MIB
	CISCO-IGMP-FILTER-MIB	OLD-CISCO-FLASH-MIB
	CISCO-IMAGE-MIB	OLD-CISCO-INTERFACES-MIB
	CISCO-IP-STAT-MIB	OLD-CISCO-IP-MIB
	CISCO-LAG-MIB	OLD-CISCO-MEMORY-MIB
	CISCO-LICENSE-MGMT-MIB	OLD-CISCO-SYS-MIB<
	CISCO-MAC-AUTH-BYPASS-MIB	OLD-CISCO-SYSTEM-MIB
	CISCO-MAC-NOTIFICATION-MIB	OLD-CISCO-TCP-MIB
	CISCO-MEMORY-POOL-MIB	OLD-CISCO-TS-MIB
	CISCO-PAE-MIB	• RMON-MIB
	CISCO-PAGP-MIB	RMON2-MIB
	CISCO-PING-MIB	• SMON-MIB
	CISCO-PORT-QOS-MIB	SNMP-COMMUNITY-MIB
	CISCO-PORT-SECURITY-MIB	SNMP-FRAMEWORK-MIB
	CISCO-PORT-STORM-CONTROL-MIB	SNMP-MPD-MIB
	CISCO-PRIVATE-VLAN-MIB	SNMP-NOTIFICATION-MIB
	CISCO-PROCESS-MIB	SNMP-PROXY-MIB
	CISCO-PRODUCTS-MIB	SNMP-TARGET-MIB
	CISCO-RESILIENT-ETHERNET-PROTOCOL-MIB	SNMP-USM-MIB
	CISCO-RTTMON-ICMP-MIB	SNMP-VIEW-BASED-ACM-MIB
	CISCO-RTTMON-IP-EXT-MIB	SNMPv2-MIB
	CISCO-RTTMON-MIB	• TCP-MIB
	CISCO-RTTMON-RTP-MIB	• UDP-MIB

Table 8. SFP Transceivers

Part Number	Specification	SFP Type	Max Distance	Cable Type	Temp Range [*]	DOM Support
GLC-FE-100FX-RGD=	100BASE-FX	FE	2km	MMF	IND	Yes
GLC-FE-100LX-RGD	100BASE-LX10	FE	10km	SMF	IND	Yes
GLC-FE-T-I=	100BASE-T	FE	100m	Copper	IND	NA
GLC-FE-100FX=	100BASE-FX	FE	2km	SMF	COM	No
GLC-FE-100LX=	100BASE-LX10	FE	10km	SMF	СОМ	No
GLC-FE-100EX=	100BASE-EX	FE	40km	SMF	СОМ	No
GLC-FE-100ZX=	100BASE-ZX	FE	80km	SMF	СОМ	No
GLC-FE-100BX-D=	100BASE-BX10	FE	10km	SMF	СОМ	No
GLC-FE-100BX-U=	100BASE-BX10	FE	10km	SMF	СОМ	Yes
GLC-SX-MM-RGD=	1000BASE-SX	GE	550m	MMF	IND	Yes
GLC-LX-SM-RGD=	1000BASE-LX/LH	GE	550m/10km	MMF/SMF	IND	Yes
GLC-ZX-SM-RGD=	1000BASE-ZX	GE	70km	SMF	IND	Yes
GLC-BX40-U-I=	1000BASE-BX40	GE	40km	SMF	IND	Yes
GLC-BX40-D-I=	1000BASE-BX40	GE	40km	SMF	IND	Yes
GLC-BX40-DA-I=	1000BASE-BX40	GE	40km	SMF	IND	Yes
GLC-BX80-U-I=	1000BASE-BX80	GE	80km	SMF	IND	Yes
GLC-BX80-D-I=	1000BASE-BX80	GE	80km	SMF	IND	Yes
GLC-SX-MMD=	1000BASE-SX	GE	550m	MMF	EXT	Yes

Part Number	Specification	SFP Type	Max Distance	Cable Type	Temp Range [*]	DOM Support
GLC-LH-SMD=	1000BASE-LX/LH	GE	550m/10km	MMF/SMF	EXT	Yes
GLC-EX-SMD=	1000BASE-EX	GE	40km	SMF	EXT	Yes
GLC-ZX-SMD=	1000BASE-ZX	GE	70km	SMF	EXT	Yes
GLC-BX-D=	1000BASE-BX10	GE	10km	SMF	СОМ	Yes
GLC-BX-U=	1000BASE-BX10	GE	10km	SMF	COM	Yes
CWDM-SFP-xxxx= (8 freq)	CWDM 1000BASE-X	GE		SMF	СОМ	Yes
DWDM-SFP-xxxx= (40 freq)	DWDM1000BASE-X	GE		SMF	СОМ	Yes
SFP-GE-S=	1000BASE-SX	GE	550m	MMF	EXT	Yes
SFP-GE-L=	1000BASE-LX/LH	GE	550m/10km	MMF/SMF	EXT	Yes
SFP-GE-Z=	1000BASE-ZX	GE	70km	SMF	EXT	Yes
GLC-SX-MM=	1000BASE-SX	GE	550m	MMF	СОМ	No
GLC-LH-SM=	1000BASE-LX/LH	GE	550m/10km	MMF/SMF	COM	No
GLC-ZX-SM=	1000BASE-ZX	GE	70km	SMF	СОМ	Yes
GLC-TE=	1000BASE-T	GE	100m	Copper	EXT	NA
GLC-T=	1000BASE-T	GE	100m	Copper	СОМ	NA

Note: For DOM support and for first software release supporting SFP, refer to http://www.cisco.com/en/US/products/hw/modules/ps5455/products device support tables list.html

MMF = multi-mode fiber

SMF = Single-mode fiber

Warranty Information

Warranty information is available at http://www.cisco-servicefinder.com/warrantyfinder.aspx.

Service and Support

Cisco is committed to reducing your total cost of ownership (TCO). We offer a portfolio of technical support services to help ensure that products operate efficiently, remain highly available, and benefit from the most up-to-date system software. The services and support programs described in Table 7 are available as part of the Cisco Desktop Switching Service and Support solution and are available directly from Cisco and through resellers.

Table 9. Cisco Services and Support Programs

Advanced Services • Cisco Total Implementation Solutions (TIS), Project management Supplements existing staff av ailable directly from Cisco • Site survey, configuration, and deployment • Helps ensure that functions meet needs • Cisco Packaged TIS, av ailable through • Installation, text, and cutover Mitigates risk Training • Helps enable proactive or expedited issue Cisco SMARTnet[®] and SMARTnet Onsite resolution • Major moves, adds, and changes support, available directly from Cisco • Lowers TCO by taking advantage of Cisco • Design review and product staging Cisco Packaged SMARTnet support expertise and knowledge program, available through resellers • 24-hour access to software updates · Reduces network downtime • Cisco SMB Support Assistant • Web access to technical repositories • Telephone support through the Cisco Technical Assistance Center (TAC) • Advance replacement of hardware parts

Cisco Capital

Financing to Help You Achieve Your Objectives

Cisco Capital can help you acquire the technology you need to achieve your objectives and stay competitive. We can help you reduce CapEx. Accelerate your growth. Optimize your investment dollars and ROI. Cisco Capital financing gives you flexibility in acquiring hardware, software, services, and complementary third-party equipment. And there's just one predictable payment. Cisco Capital is available in more than 100 countries. Learn more.

For More Information

For more information about Cisco products, contact:

United States and Canada: 800 553-6387

Europe: 32 2 778 4242Australia: 612 9935 4107Other: 408 526-7209

 Cisco Industrial Ethernet 2000 (IE 2000) Series Switches: http://www.cisco.com/en/US/partner/products/ps12451/index.html.



Americas Headquarters Cisco Systems, Inc. San Jose, CA Asia Pacific Headquarters Cisco Systems (USA) Pte. Ltd. Singapore Europe Headquarters Cisco Systems International BV Amsterdam, The Netherlands

 $Cisco\ has\ more\ than\ 200\ offices\ worldwide.\ Addresses,\ phone\ numbers,\ and\ fax\ numbers\ are\ listed\ on\ the\ Cisco\ Website\ at\ www.cisco.com/go/offices.$

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: www.cisco.com/go/trademarks. Third party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)

Printed in USA C78-730729-11 05/17