

**2001
2002**

7½-Digit High Performance Multimeter 8½-Digit High Performance Multimeter



- True 7½- (Model 2001) or 8½-digit (Model 2002) resolution
- Exceptional measurement integrity with high speed
- Broad range of built-in measurement functions
- Built-in 10 channel scanner option
- IEEE-488.2 and SCPI compatible
- Model 2002 has HP 3458A emulation mode

High Accuracy ACV Measurements

A patented circuit design makes the 2001 and 2002's AC measurements several times more accurate than competitive DMMs, thus maintaining very good accuracy (better than 0.1%) down to 1Hz. The wide bandwidth of these DMMs allows for accurate measurements of high frequency AC signals without the need for a special AC meter. Both the 2001 and 2002 feature TRMS AC, Average AC, Peak AC, AC+DC, and Crest Factor measurement capability for a wide variety of applications.

Built-In Scanner (Multiplexer) Options

With the addition of a plug-in scanner card, it becomes a complete scan and measure system for applications involving up to ten measurement points. The additional resolution and measurement ranges provided by the 2002 make it an excellent choice for production test, design verification, and metrology applications where high accuracy is critical.

DMM users whose applications demand exceptional resolution, accuracy, and sensitivity combined with high throughput now have two attractive alternatives to high priced, high-end DMMs. Keithley's 7½-digit Model 2001 and 8½-digit Model 2002 High Performance Digital Multimeters not only deliver performance specifications usually associated only with instruments that cost thousands more, but they also offer a broad range of functions not typically available from DMMs.

True 7½- (or 8½-) Digit Resolution

While other DMMs may claim 7½- or 8½-digit resolution, those instruments must average multiple readings to extend their resolution. The resolution specifications of the 2001 and 2002 are based on a 28-bit A/D converter that provides the resolution needed to discern smaller changes. This higher resolution also provides greater dynamic range, making it possible to measure from 1µV to 20V on a single range, thus avoiding range-shift errors and delays.

High Throughput, High Accuracy DCV and Resistance Measurements

In applications where high throughput is critical, both the Model 2001 and 2002 provide more than 2000 readings per second at 4½-digit resolution. At 7½ digits, the Model 2002 maintains full rated accuracy at reading rates up to 44/second on DCV and ohms.

The Model 2002 uses a unique single-phase method for 4-wire ohms measurements. This makes it twice as fast for a given power line cycle rate. This also eliminates errors due to changing lead resistances that can result from fast test handlers. A built-in "open-lead" detection circuit also eliminates many production test problems.

ACCESSORIES AVAILABLE

TEST LEADS AND PROBES

5805	Kelvin Probes, 0.9m (3 ft)
8606	High Performance Modular Probe Kit

CABLES/ADAPTERS

7007-1	Shielded GPIB Cable, 1m (3.3 ft)
7007-2	Shielded GPIB Cable, 2m (6.6 ft)
7009-5	RS-232 Cable

RACK MOUNT KITS

4288-1	Single Fixed Rack Mount Kit
4288-4	Side by Side Rack Mount Kit

OTHER

KPC-488.2	IEEE-488.2 Interface Card for the ISA Bus
KPCI-488	IEEE-488 Interface/Controller for the PCI Bus
KUSB-488	IEEE-488.2 USB-to-GPIB Interface Adapter



High resolution, high accuracy DMMs

DIGITAL MULTIMETERS & SYSTEMS

1.888.KEITHLEY (U.S. only)

www.keithley.com

KEITHLEY

A GREATER MEASURE OF CONFIDENCE

2001 Condensed Specifications

DC VOLTS

RANGE	RESOLUTION	INPUT RESISTANCE	ACCURACY ±(ppm of reading + ppm of range) 90 Days
200 mV	10 nV	>10 GΩ	25 + 6
2 V	100 nV	>10 GΩ	18 + 2
20 V	1 μV	>10 GΩ	18 + 4
200 V	10 μV	10 MΩ ±1%	27 + 3
1000 V	100 μV	10 MΩ ±1%	31 + 6

RESISTANCE

RANGE	RESOLUTION	CURRENT SOURCE	ACCURACY ±(ppm of reading + ppm of range) 90 Days
20 Ω	1 μΩ	9.2 mA	52 + 7
200 Ω	10 μΩ	0.98 mA	36 + 7
2 kΩ	100 μΩ	0.98 mA	33 + 4
20 kΩ	1 mΩ	89 μA	32 + 4
200 kΩ	10 mΩ	7 μA	72 + 4.5
2 MΩ	100 mΩ	770 nA	110 + 4.5
20 MΩ	1 Ω	70 nA	560 + 4.5
200 MΩ	10 Ω	4.4 nA	10000 + 100
1 GΩ	100 Ω	4.4 nA	20000 + 100

DC AMPS

RANGE	RESOLUTION	MAXIMUM BURDEN VOLTAGE	ACCURACY ±(ppm of reading + ppm of range) 90 Days
200 μA	10 pA	0.25 V	300 + 25
2 mA	100 pA	0.31 V	300 + 20
20 mA	1 nA	0.4 V	300 + 20
200 mA	10 nA	0.5 V	300 + 20
2 A	100 nA	1.5 V	600 + 20

GENERAL

POWER

Voltage: 90–134V and 180–264V, universal self-selecting.
Frequency: 50Hz, 60Hz, or 400Hz self-identifying.
Consumption: <55 VA.

ENVIRONMENT

Operating Temperature: 0° to 50°C.
Storage Temperature: –40° to +70°C.
Humidity: 80% R.H., 0° to 35°C.
Altitude: 4,500m (15,000 ft) operating; 12,000m (40,000 ft.) non-operating.

PHYSICAL

Case Dimensions: 90mm high × 214mm wide × 369mm deep (3½ in × 8½ in × 14½ in).
Unit Weight: 4.2kg (9.2 lbs).

STANDARDS

EMI/RFI: Conforms to VDE 0871B (per Vfg 1046/1984), IEC 801-2, FCC part 15 Class B, CISPR-22 (EN55022).
Safety: Conforms to IEC348, CAN/CSC22.2 No. 231, MIL-T-28800E1.

FREQUENCY COUNTER

RANGE: 1Hz–15MHz.

ACCURACY: ±(0.03% of reading).

DC IN-CIRCUIT CURRENT

RANGE: 100μA to 12A.

ACCURACY: ±(5% + 2 counts) over 2 years.

TRACE RESISTANCE: 1mΩ to 10Ω typical.

TEMPERATURE

Built-in linearization for J, K, N, T, E, R, S, B thermocouple types to ITS-90 and 100Ω2477com(tte speci6 T6cc 11.s,564f 0 Tw .14)1031 4771032L-

1.888.KEITHLEY (U.S. only)

www.keithley.com

KEITHLEY

A GREATER MEASURE OF CONFIDENCE