

## Foot element - UM 25/45-FEO 200 - 2959434

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Foot element, is inserted in the profile housing, limit stop with screw. Mounted at right angles to the NS 35/7.5 DIN rail

### Your advantages

- ✓ UM ...-SES lateral element offers options for labeling with Phoenix Contact marking material
- ✓ Fast mounting
- ✓ Flexible size and shape
- ✓ Inexpensive as a result of reducing the number of separate housing parts
- ✓ High degree of mechanical stability by screwing the lateral elements to the profile
- ✓ The UMK-BF mounting flange enables modules to be mounted directly on the wall
- ✓ Cable fixing by means of UM ...-SEK lateral element (fixed using cable binders, not supplied as standard)



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 117610
GTIN	4017918117610
Weight per Piece (excluding packing)	6.660 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Product properties

Brief article description	Foot element
Type	UM 25/45-FEO 200
Order No.	2959434
Housing type	Press-drawn section housings

#### Dimensions

# Foot element - UM 25/45-FEO 200 - 2959434

## Technical data

### Material specifications

Housing material	Polyamide
Color (RAL)	green
Flammability rating according to UL 94	V0

### Packaging specifications


Pieces per package	10
Denomination packing units	Pcs.

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


## Drawings

Dimensional drawing



# Foot element - UM 25/45-FEO 200 - 2959434

Dimensional drawing



## Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779
ETIM 6.0	EC002779

# Foot element - UM 25/45-FEO 200 - 2959434

## Classifications

### ETIM

ETIM 7.0	EC002779
----------	----------

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Approvals

### Approvals

---

Approvals


UL Recognized / EAC

---

Ex Approvals

---

### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 240868
---------------	---	---	---------------

EAC		B.01742
-----	---	---------