

Conductor marking collar - SD-WMTBS (NEUTRAL) CC - 0826637

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, yellow: without print, mounting type: slide-on, cable diameter: > 16 mm, lettering field size: 4.3 x 26 mm


The figure shows the version SD-WMTBS (S) YE

Your advantages

- The printed individual markers are pushed onto the corresponding holders
- Cable markers for marking cables and conductors with larger cross sections



Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 414494
GTIN	4046356414494
Weight per Piece (excluding packing)	0.140 g
Custom tariff number	39269097
Country of origin	Sweden
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	11.3 mm
Width (a)	4.3 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

General

Note	Please specify the required marking with order: Minimum order per imprint: 1 packing unit
------	---

Conductor marking collar - SD-WMTBS (NEUTRAL) CC - 0826637

Technical data

General

Color	yellow
Type	Marking strip/label
Components	Free from silicone and cadmium
Flammability rating according to UL 94	V2
Material	Polyvinyl chloride
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	slide-on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

Conductor marking collar - SD-WMTBS (NEUTRAL) CC - 0826637

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Assortment box

Range box - SORTI 1/10 - 5020425



Assortment box, dimensions: 170 x 105 x 32 mm, 10 compartments, compartment size: 50 x 32 mm

Range box - SORTI 2/12 - 5020674



Assortment box, dimensions: 210 x 105 x 36 mm, 12 compartments, compartment size: 57 x 32 mm

Conductor marking collar - SD-WMTBS (NEUTRAL) CC - 0826637

Accessories

Range box - SORTI 3/ 7 - 5020645



Assortment box, dimensions: 250 x 170 x 46 mm, 7 compartments, compartment size 1: 98 x 39 mm, compartment size 2: 66 x 243 mm

Range box - SORTI 3/ 8 - 5020438



Assortment box, dimensions: 250 x 170 x 46 mm, 8 compartments, compartment size 1: 48 x 39 mm, compartment size 2: 98 x 39 mm, compartment size 3: 98 x 80 mm, compartment size 4: 66 x 243 mm

Range box - SORTI 3/18 - 5028731



Assortment box, dimensions: 250 x 170 x 46 mm, 18 compartments, compartment size 1: 48 x 39 mm, compartment size 2: 66 x 39 mm

Range box - SORTI 4/8 - 5145180



Assortment box, 8 compartments

Range box - SORTI 4/12 - 5020658



Assortment box, 12 compartments external dimensions 335 x 225 x 55 mm, material: Polystyrene

Conductor marking collar - SD-WMTBS (NEUTRAL) CC - 0826637

Accessories

Range box - SORTI 4/24 - 5031524



Assortment box, dimensions: 335 x 225 x 55 mm, 24 compartments, compartment size 1: 53 x 53 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>