

# Configuration memory - FL MEM PLUG/MRM - 2891275


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Exchangeable configuration memory of the device settings for simple device exchange and set-up. In addition, the Media Redundancy Manager (MRM) license for use is stored within the Media Redundancy protocol (MRP).



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 165433
GTIN	4046356165433
Weight per Piece (excluding packing)	19.000 g
Custom tariff number	84717098
Country of origin	Germany

## Technical data

### Dimensions

Width	16 mm
Height	49 mm

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

### Function

Basic functions	Configuration memory and manager for the media redundancy protocol (MRP)
-----------------	--

### General

Mounting type	In the host system
Type AX	Fine granularity

# Configuration memory - FL MEM PLUG/MRM - 2891275

## Technical data

### General

Net weight	19 g
------------	------

### Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6-2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion A
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Test standard	IEC 61000-4-8 (immunity to magnetic fields)
Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A

### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Noise emission	EN 61000-6-3/-4
Noise immunity	EN 61000-6-2:2005

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	27242200
eCl@ss 5.1	27250500
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

## Configuration memory - FL MEM PLUG/MRM - 2891275

### Classifications

#### ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	32101606
UNSPSC 18.0	32101606
UNSPSC 19.0	32101606
UNSPSC 20.0	32101606
UNSPSC 21.0	32101606